



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GK6429 2/0-250 Cop Ground Conn

Burndy LLC

Catalog Number	GK6429
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, 3 Cables to Rod or Pipe, 2/0 Awg (Sol) -250 Kcmil, 3/8" Pipe, 5/8"-3/4" Rod.
Weight per unit	1.7 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Bolt Size	1/2 in
Material	Copper Alloy, Cast

Descriptions

Description	2/0-250 COP GROUND CONN
extra long description	BUR GK6429 2/0-250 (3) CU .8 GRD
Long Description	Mechanical Grounding Connector, 3 Cables to Rod or Pipe, 2/0 AWG (Sol) -250 kcmil, 3/8" Pipe, 5/8"-3/4" Rod.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining Three Equal Cables To Rod Or Tube, Cable Grooves Take A Wide Range Of Cable, High Copper Alloy Cast Body And DURIUM U-Bolts, Nuts, And Lockwashers Make The GK Suitable For Direct Burial In Soil Or Concrete, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, Ground Rod Size: 5/8 - 3/4 IN, Tube (ips) Size: 3/8 IN, Width: 3-1/2 IN, Height: 2-7/8 IN, Installation Torque: 480 IN-LB

Manufacturer Information

Brand	BURNDY
GTIN	00781810233535
Manufacturers Part Number	GK6429
UPC	781810233535

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Three Cables to Rod or Tube

Packaging

Carton	1
Package	6
Weight Per each	1.71



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

For Joining Three Equal Copper Cables To Rod Or Tube, Direct
Burial In Earth Or Concrete

standard

UL467