



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GL1038 1/0 1-Hole Compression Lug 3/8" Bolt

Nsi Industries

Catalog Number	GL1038
Manufacturer	Nsi Industries
Description	1 Hole Short Barrel Copper Compression Lug W/ Peep Hole 1/0 Awg - 3/8" Bolt Short Barrel Copper Compression Lugs With Peep Hole Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	0.0400 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Cable Size	1/0 AWG (STR)
Material	Copper
Number of Holes	1
Stud Size	3/8
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Pink
Finish	Tin Plated

Dimensions and Weight

Size	L=1.83 - W=.739 - OD=.519 - ID=.389
------	-------------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	1/0 1-HOLE COMPRESSION LUG 3/8" BOLT
extra long description	NSI GL1038 CU CMP Lug Short 1/0 AWG
Features	1 Hole Short Barrel Copper Compression Lug w/ Peep Hole 1/0 AWG - 3/8" Bolt Short Barrel Copper Compression Lugs with Peep Hole is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	1 Hole Short Barrel Copper Compression Lug w/ Peep Hole 1/0 AWG - 3/8" Bolt Short Barrel Copper Compression Lugs with Peep Hole is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	Cu CMP Lug Short 1/0 Awg 3/8 Bolt Size
Special Features	1/0 AWG (STR) - 3/8 Mounting Hole

Manufacturer Information

Brand	NSi
GTIN	00662381036070
Manufacturers Part Number	GL1038
UPC	662381036070

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Short Barrel - One Hole

Packaging

Carton	1
Package	50
Weight Per each	0.04

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	3/8 Mounting Hole
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)