



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GL810 #8 1-Hole Compression Lug #10 Bolt

Nsi Industries

Catalog Number	GL810
Manufacturer	Nsi Industries
Description	1 Hole Short Barrel Copper Compression Lug W/ Peep Hole 8 Awg - #10 Bolt Short Barrel Copper Compression Lugs With Peep Hole Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	0.0200 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Cable Size	# 8 AWG (STR)
Material	Copper
Number of Holes	1
Stud Size	#10
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Red
Finish	Tin Plated

Dimensions and Weight

Size	L=1.20 - W=.420 - OD=.270 - ID=.170
------	-------------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	#8 1-HOLE COMPRESSION LUG #10 BOLT
extra long description	NSI GL810 CU CMP Lug Short 8 AWG #1
Features	1 Hole Short Barrel Copper Compression Lug w/ Peep Hole 8 AWG - #10 Bolt Short Barrel Copper Compression Lugs with Peep Hole is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	1 Hole Short Barrel Copper Compression Lug w/ Peep Hole 8 AWG - #10 Bolt Short Barrel Copper Compression Lugs with Peep Hole is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	Cu CMP Lug Short 8 Awg #10 Bolt Size
Special Features	# 8 AWG (STR) - # 10 Mounting Hole

Manufacturer Information

Brand	NSi
GTIN	00662381036001
Manufacturers Part Number	GL810
UPC	662381036001

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Short Barrel - One Hole

Packaging

Carton	1
Package	100
Weight Per each	0.02

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	# 10 Mounting Hole
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)