



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GLC440DB BRZ GND Clamp

Nsi Industries

Catalog Number	GLC440DB
Manufacturer	Nsi Industries
Description	Nsi GLC-440DB Heavy Duty Direct Burial Ground Clamps Grip On Pipes Between 1-2-1/2" to 4" In Diameter and Are The Ultimate Ground Clamps For Securing Just About Any Size Ground Wire In Just About Any Application. The Bronze Body and Pre-Assembled 304 Stainless Steel Screws Are Made Of Economical, High-Quality Metals That Provide Durable Performance In A Range Of Applications. The Lay-In Lug Design Of These Clamps Provides Ultimate Flexibility When Securing Large Conductors and Can Accommodate Wires In The
Weight per unit	1.1 (lbs/each)
Product Category	Grounding & Bonding Equipment

Features

Warranty	1 YEAR
----------	--------

Material, Color, and Finish

Clamp Material	8 -4/0 STR
Insulation Material	Silicon Bronze



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	BRZ GND CLAMP
extra long description	NSI GLC-440DB Ground Clamp Lay-In 2
Features	NSI grounding and bonding products rise to the occasion in a wide variety of indoor and outdoor environments with excellent material quality and flexible designs. These heavy-duty bronze ground clamps with lay-in lugs offer the ultimate solution for grounding large wires in just about any application. Grips onto copper water pipes, tubing, rebar and ground rods using 304 stainless steel screws to tighten the clamp, then grounding conductor is secured in place using a lay-in lug design for ultimate flexibil
Long Description	NSI GLC-440DB Heavy Duty Direct Burial Ground Clamps grip on pipes between 1-2-1/2" to 4" in diameter and are the ultimate ground clamps for securing just about any size ground wire in just about any application. The bronze body and pre-assembled 304 stainless steel screws are made of economical, high-quality metals that provide durable performance in a range of applications. The lay-in lug design of these clamps provides ultimate flexibility when securing large conductors and can accommodate wires in the
Product Type	Ground Clamp Lay-In 2 1/2-4" DB Rated
Special Features	2 1/2-4 Pipe Size

Manufacturer Information

Brand	NSi
GTIN	00662381007193
Manufacturers Part Number	GLC-440DB
UPC	662381007193

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Heavy Duty Direct Burial Lay-In Lug

Packaging

Carton	1
Package	3
Weight Per each	1.1

Uses, Certifications, and Standards

Application	Grounding Wire
standard	cULus