



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GD1929 250 Parallel Ground Conn

Burndy LLC

Catalog Number	GD1929
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 2/0 Awg (Sol.) - 250 Kcmil, 2-1/2" to 2-7/8" Rod, 2-1/2" Pipe.
Weight per unit	1.2 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Copper Alloy, Cast
----------	--------------------

### Descriptions

Description	250 PARALLEL GROUND CONN
extra long description	BUR GD1929 2/0SOL-250, 2 1/2 IPS,
Long Description	Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 2/0 AWG (Sol.) - 250 kcmil, 2-1/2" to 2-7/8" Rod, 2-1/2" Pipe.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Range Of Two Parallel Cables To Rod Or Pipe, Especially Good For Grounding Fence Posts, High Copper Alloy Cast Body With DURUM U-Bolts, Nuts, And Lockwashers Make The GD Suitable For Burial In Ground Or Concrete, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, Raised Floor: No, Tube (ips) Size: 2-1/2 IN, Ground Rod Size: 2-1/2 - 2-7/8 IN, Height: 5 IN, Installation Torque: 240 IN-LB, Width: 4-1/4 IN

### Manufacturer Information

Brand	BURNDY
GTIN	00781810238950
Manufacturers Part Number	GD1929
UPC	781810238950

### Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GD

### Packaging

Carton	1
Weight Per each	1.245



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

For Joining A Range Of Two Parallel Copper Cables To Rod Or  
Pipe And Burial In Ground Or Concrete

standard

UL467