



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GD2029 250 Parallel Ground Conn *Burndy LLC*

Catalog Number	GD2029
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 2/0 Awg (Sol.) - 250 Kcmil, 3" to 3-1/2" Rod, 3" Pipe.
Weight per unit	1.8 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper Alloy, Cast
----------	--------------------

Descriptions

Description	250 PARALLEL GROUND CONN
extra long description	BUR GD2029 2/0SOL-250, 3 IPS, 2 CO
Long Description	Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 2/0 AWG (Sol.) - 250 kcmil, 3" to 3-1/2" Rod, 3" Pipe.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Range Of Two Parallel Cables To Rod Or Pipe, Especially Good For Grounding Fence Posts, High Copper Alloy Cast Body With DURIUM U-Bolts, Nuts, And Lockwashers Make The GD Suitable For Burial In Ground Or Concrete, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, Raised Floor: No, Ground Rod Size: 3 - 3-1/2 IN, Tube (ips) Size: 3 IN, Height: 5-5/8 IN, Width: 4-7/8 IN, Installation Torque: 240 IN-LB

Manufacturer Information

Brand	BURNDY
GTIN	00781810260395
Manufacturers Part Number	GD2029
UPC	781810260395

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GD

Packaging

Carton	1
Weight Per each	1.77



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

For Joining A Range Of Two Parallel Copper Cables To Rod Or
Pipe And Burial In Ground Or Concrete

standard

UL467