



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GLL610C 2"GRND BSH 1/0-8AWG Lug

Crouse-Hinds

Catalog Number	GLL610C
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series GLL Grounding Bushing, Rigid/Imc, Copper Lug, #1/0-8 Awg, Malleable Iron, 105°C Temperature Rating, Threaded, 2"
Weight per unit	0.4000 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Threaded
dimensions	2.7500 IN X 2.7500 IN X 0.8800 IN
Material	Malleable Iron Body, Plastic Throat Liner

Dimensions and Weight

Size	2 in
------	------

Descriptions

Description	2"GRND BSH 1/0-8AWG LUG
extra long description	MIDWEST GLL6 10C 2 GRND BUSH 105C I
Features	Crouse-Hinds series grounding bushings are used with threaded and threadless rigid/IMC conduit to provide a means of grounding conduit through an insulated bushing.
Long Description	Eaton Crouse-Hinds series GLL grounding bushing, Rigid/IMC, Copper lug, #1/0-8 AWG, Malleable iron, 105°C temperature rating, Threaded, 2"
Product Type	2 GRND Bush 105C Insul 1 to 8 Copp Lug
Special Features	With 8 To 1/0 AWG Copper Lug for Copper Grounding Conductor, Weight 40 Lb per 100

Manufacturer Information

Brand	Eaton
GTIN	00784564123466
Manufacturers Part Number	GLL6 10C
UPC	784564123466

Taxonomies, Classifications, and Categories

Category Description	COUPLINGS, ADAPTERS, REDUCERS, BUSHINGS, & CAPS
Type	Grounding bushing

Packaging

Carton	10
Weight Per each	0.4



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL, CSA
Temperature Rating	105 DEG C