



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GFBFST20GY 20A Com Self Test Faceless GFR Gray

Hubbell Wiring Devices

Catalog Number	GFBFST20GY
Manufacturer	Hubbell Wiring Devices
Description	Power Protection Devices, Self Test Faceless Gfci, 20A 125V, 2-Pole 3-Wire Grounding, Gray
Weight per unit	0.3500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Terminal Screws
Number of Wires	3-Wire Grounding
pallet quantity	2400
Phase	1
Poles	2-Pole
Voltage Rating	125
Wattage	2500
Wire Size	#14 to #12

Dimensions and Weight

Size	Standard Sized Product
------	------------------------

Descriptions

Description	20A COM SELF TEST FACELESS GFR GRAY
extra long description	HWDK GFBFST20GY 20A COM SELF TEST F
Features	AUTOGUARD® Self Test Technology 1st introduced by Hubbell over 10 years ago...self test monitoring now required in 2015 UL 943 GFCI Safety Standard... Hubbell AUTOGUARD® GFCI receptacles continually test and monitor for "people protection capability" automatically. This patented safety feature includes disconnecting power to the receptacle if critical components are damaged and GFCI protection is lost. GFCI auto-monitoring is conducted continuously within every 30 seconds. Also, clear visual indicators are p
Long Description	Power Protection Devices, Self Test Faceless GFCI, 20A 125V, 2-Pole 3-Wire Grounding, Gray
Product Type	20A Com Self Test Faceless GFR Gray
Special Features	Blank Face, Self Test



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Hubbell Wiring Devices
GTIN	00883778122187
Manufacturers Part Number	GFBFST20GY
series	Heavy Duty
UPC	883778122187

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	STANDARD

Packaging

Carton	10
Package	1
Weight Per each	0.35

Uses, Certifications, and Standards

Application	Commercial Grade
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
standard	Meets All NEC® Requirements