HUBBELL
Wiring Device-Kellems

Power Protection Devices, Receptacle, Self Test, GFCI, TR, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R, Ivory



By Hubbell Wiring Device-Kellems
Catalog # GFRTR20I

Power Protection Devices, Receptacle, Self Test, GFCI, TR, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R, Ivory.

General

Catalog Number	GFRTR20I
Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Specifications	• Base - Nylon • Face - Nylon • Ground Contacts - Brass • Mounting Screws - Zinc plated steel • Mounting Strap - Zinc plated steel • Power Contacts - Brass
Style	Standard
Type	Tamper-Resistant
UPC	883778999666

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating Description	125 V

Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-20R

Logistics

Carton Quantity	10

Product Assets

Catalog Page - WDK K-4 Catalog Page
Catalogs - WDK Catalog Full 2024
Engineering Drawing - M-14627 AutoCAD Drawing
Installation Manuals - PD2987
Literature - Commercial GFCI Receptacles
Literature - FREQUENTLY ASKED QUESTIONS Commercial GFCI Receptacles
Sales Drawings - M14627
Specifications - WIRING_GFRTR20I_spec

©2025 Hubbell Incorporated. All rights reserved

HUBBELL
Wiring Device-Kellems

Power Protection Devices, Receptacle, Self Test, GFCI, TR, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R, Ivory



By Hubbell Wiring Device-Kellems
Catalog # GFRTR20I

Power Protection Devices, Receptacle, Self Test, GFCI, TR, Commercial Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5- 20R, Ivory.

General

Catalog Number	GFRTR20I
Color	Ivory
EU RoHS Indicator	Contact Manufacturer
Series	Heavy Duty
Specifications	• Base - Nylon • Face - Nylon • Ground Contacts - Brass • Mounting Screws - Zinc plated steel • Mounting Strap - Zinc plated steel • Power Contacts - Brass
Style	Standard
Type	Tamper-Resistant
UPC	883778999666

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating Description	125 V

Certifications And Compliance

Industry Standard(s)	Meets All NEC® Requirements
Nema Rating	5-20R

Logistics

Carton Quantity	10

Product Assets

Catalog Page - WDK K-4 Catalog Page
Catalogs - WDK Catalog Full 2024
Engineering Drawing - M-14627 AutoCAD Drawing
Installation Manuals - PD2987
Literature - Commercial GFCI Receptacles
Literature - FREQUENTLY ASKED QUESTIONS Commercial GFCI Receptacles
Sales Drawings - M14627
Specifications - WIRING_GFRTR20I_spec

©2025 Hubbell Incorporated. All rights reserved