



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## GRP1140 11" 40LB Natural CBL Tie

*Nsi Industries*

Catalog Number	GRP1140
Manufacturer	Nsi Industries
Description	The Powergrp GRP-1140 100-Count Resealable Pack Of Type 21 Natural-Colored General-Purpose Cable Ties Are 11" Long, With 40LB Of Tensile Strength For Professional Applications. They're Made From Polyamide 6, 6 Nylon, Resulting In A High Mechanical Strength and A Wide Temperature Range (-40 F to 185 F). Fasten These 11" Cables Ties Around A Wide Range Of Equipment With A Bundle Diameter Between .08" (2MM) and 2.99" (76MM), Using The Bent Tips and Serrated Locking Mechanism to Form An Effortless and Sec
Weight per unit	0.3450 (lbs/each)
Product Category	Tools & Testers

### Features

Warranty	1 YEAR
----------	--------

### Material, Color, and Finish

Finish	Natural
--------	---------

### Descriptions

Description	11" 40LB NATURAL CBL TIE
extra long description	NSI GRP-1140 PowerGRP Cable Tie Nat
Features	PowerGRP cable ties are a comprehensive product line of specialty ties, strong enough to handle industrial environments and ideally suited for demanding applications. The GRP-1140 ties combine a self-locking design with a general purpose 40lb tensile strength rating, guaranteeing that these ties won't break easily. The GRP in our name stands for Guaranteed Rugged and Powerful, just one way we show that we're fully committed to building strong ties for professional users. GRP-1140 ties are waterproof an
Long Description	The PowerGRP GRP-1140 100-Count Resealable Pack of Type 21 Natural-Colored General-Purpose Cable Ties are 11" long, with 40lb of tensile strength for professional applications. They're made from polyamide 6,6 nylon, resulting in a high mechanical strength and a wide temperature range (-40 F to 185 F). Fasten these 11" cables ties around a wide range of equipment with a bundle diameter between .08" (2mm) and 2.99" (76mm), using the bent tips and serrated locking mechanism to form an effortless and sec
Product Type	Powergrp Cable Tie Natural 11" 40LB (100PK)



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	NSi
GTIN	00662381009159
Manufacturers Part Number	GRP-1140
UPC	662381009159

## Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
----------------------	--

## Availability

minimum qty	100
-------------	-----

## Packaging

Carton	1
Package	100
Weight Per each	0.345

## Uses, Certifications, and Standards

Temperature Rating	-40F to 185F
--------------------	--------------