



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## GRP1140 11" 40LB Natural CBL Tie

*Nsi Industries*

|                  |  |
|------------------|--|
| Catalog Number   | GRP1140  |
| Manufacturer     | Nsi Industries   |
| Description      | The Powergrp GRP-1140 100-Count Resealable Pack Of Type 21 Natural-Colored General-Purpose Cable Ties Are 11" Long, With 40LB Of Tensile Strength For Professional Applications. They're Made From Polyamide 6, 6 Nylon, Resulting In A High Mechanical Strength and A Wide Temperature Range (-40 F to 185 F). Fasten These 11" Cables Ties Around A Wide Range Of Equipment With A Bundle Diameter Between .08" (2MM) and 2.99" (76MM), Using The Bent Tips and Serrated Locking Mechanism to Form An Effortless and Sec |
| Weight per unit  | 0.3450 (lbs/each)  |
| Product Category | Tools & Testers  |

### Features

|          |        |
|----------|--------|
| Warranty | 1 YEAR |
|----------|--------|

### Material, Color, and Finish

|        |         |
|--------|---------|
| Finish | Natural |
|--------|---------|

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 11" 40LB NATURAL CBL TIE  |
| extra long description | NSI GRP-1140 PowerGRP Cable Tie Nat   |
| Features               | PowerGRP cable ties are a comprehensive product line of specialty ties, strong enough to handle industrial environments and ideally suited for demanding applications. The GRP-1140 ties combine a self-locking design with a general purpose 40lb tensile strength rating, guaranteeing that these ties won't break easily. The GRP in our name stands for Guaranteed Rugged and Powerful, just one way we show that we're fully committed to building strong ties for professional users. GRP-1140 ties are waterproof an |
| Long Description       | The PowerGRP GRP-1140 100-Count Resealable Pack of Type 21 Natural-Colored General-Purpose Cable Ties are 11" long, with 40lb of tensile strength for professional applications. They're made from polyamide 6,6 nylon, resulting in a high mechanical strength and a wide temperature range (-40 F to 185 F). Fasten these 11" cables ties around a wide range of equipment with a bundle diameter between .08" (2mm) and 2.99" (76mm), using the bent tips and serrated locking mechanism to form an effortless and sec   |
| Product Type           | Powergrp Cable Tie Natural 11" 40LB (100PK)   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSi            |
| GTIN                      | 00662381009159 |
| Manufacturers Part Number | GRP-1140       |
| UPC                       | 662381009159   |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps |
|----------------------|--|

## Availability

|             |     |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 1     |
| Package         | 100   |
| Weight Per each | 0.345 |

## Uses, Certifications, and Standards

|                    |              |
|--------------------|--------------|
| Temperature Rating | -40F to 185F |
|--------------------|--------------|