



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GL638 #6 1H Cu SHRT CMP Lug

*Nsi Industries*

Catalog Number	GL638
Manufacturer	Nsi Industries
Description	1 Holeshort Barrel Copper Compression Lug W/ PEEPHOLE6 Awg-3/8" Bolt Short Barrel Copper Compression Lugs With Peepholeis A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	1.8 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Cable Size	# 6 AWG (STR)
Material	Copper
Number of Holes	1
Stud Size	3/8
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Blue
Finish	Tin Plated

### Dimensions and Weight

Size	L=1.50 - W=.420 - OD=.300 - ID=.200
------	-------------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	#6 1H CU SHRT CMP LUG
extra long description	NSI GL638 CU CMP Lug Short 6 AWG 3/
Features	1 HoleShort Barrel Copper Compression Lug w/ PeepHole6 AWG-3/8" Bolt Short Barrel Copper Compression Lugs with PeepHoleis a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	1 HoleShort Barrel Copper Compression Lug w/ PeepHole6 AWG-3/8" Bolt Short Barrel Copper Compression Lugs with PeepHoleis a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	Cu CMP Lug Short 6 Awg 3/8 Bolt Size
Special Features	# 6 AWG (STR) - 3/8 Mounting Hole

## Manufacturer Information

Brand	NSi
GTIN	00662381036247
Manufacturers Part Number	GL638
UPC	662381036247

## Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Short Barrel - One Hole

## Packaging

Carton	1
Package	100
Weight Per each	1.8

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	3/8 Mounting Hole
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)