



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **GMA3R 3A 250V Fa 5X20MM Glass Fuse** *Bussmann Fuses*

Catalog Number	GMA3R
Manufacturer	Bussmann Fuses
Description	Fuse, Fast Acting Fuse Speed, 60 Min @ 135%;2 Min @ 200 % Response Time, Ferrule End X Ferrule End Connection, 3 A, 250 V Ac, Glass (Body);Brass( End Cap) Material, Ferrule Terminal, 5.2 MM Diameter, 20 MM Overall Length
Weight per unit	0.0050 (lbs/each)
Product Category	Small Dimension Fuses

### **Features**

amperage rating	3
connection	Ferrule End X Ferrule End
dimensions	X X 0.7874 IN

### **Dimensions and Weight**

Size	5 mm Diameter X 20 mm Length
------	------------------------------

### **Descriptions**

Description	3A 250V FA 5X20MM GLASS FUSE
extra long description	EFSE GMA-3-R GMA 3A BUSS FUSE
Features	Fast-acting, glass tube 5 mm x 20 mm ferrule fuse designed to UL 248-14 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block or fuse clip. Also available with axial leads for thru-hole installation Eaton's GMA Fast-acting glass tube fuses (5 mm x 20 mm) Designed to meet UL 248-14 standards, these fuses provide dependable overcurrent protection for electronic circuits. Constructed with a glass body, they are RoHS compliant and available in two formats: Cartri
Special Features	Low Breaking Capacity, Interrupt Rating 100 Amp at 250 Vac, 10 kA at 125 Vac, Material Glass Tube, Nickel Plated Brass Endcap, ROHS Complaint

### **Manufacturer Information**

Brand	Eaton
GTIN	00051712647946
UPC	051712647946

### **Taxonomies, Classifications, and Categories**

Category Description	GLASS FUSES (and ceramic)
Type	5 x 20 mm Fast-acting glass tube fuse

### **Packaging**

Carton	5
Weight Per each	0.005



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

standard

RoHS Compliant,CE Marked