



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GRC34 3/4" GRND Rod Conn

Nsi Industries

Catalog Number	GRC34
Manufacturer	Nsi Industries
Description	We Built The Nsi GRC-34 Standard Duty Silicon Bronze Grounding Rod Clamp For Demanding Applications Including Direct Burial, Where The Simple Mechanical Design and Reliable Clamping Power Of The Screw Outperform Other Options. The GRC-34 Grounding Rod Clamp Fits Grounding Rod With A Diameter Of 3/4" and Rebar With A Diameter Of 5/8" With Room To Tighten The Clamping Screw Onto A Range Of 10 Awg Solid to 1 Awg Stranded Conductors. GRC-Family Clamps With The -SB Suffix Have A Body and Screw Made From Silicon
Weight per unit	0.1180 (lbs/each)
Product Category	Ground Rods & Grounding System

Features

Warranty	1 YEAR
----------	--------

Material, Color, and Finish

Clamp Material	10 SOL - 1 STR
Insulation Material	Silicon Bronze



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Also Known As...	Acorn
Description	Tear Drop
extra long description	3/4" GRND ROD CONN
Features	NSI GRC-34 Ground Rod Connector 3/4 NSI grounding and bonding products rise to the occasion in a wide variety of environments with excellent material quality and flexible designs. This standard duty silicon bronze grounding rod clamp is specially designed for demanding direct burial applications when ordered with a "SB" suffix, fitting down over a grounding rod and clamping solid or stranded conductors to that rod. The silicon bronze body and screw provide maximum durability and clamping force. UL-listed for direct burial in earth or con
Long Description	We built the NSI GRC-34 Standard Duty Silicon Bronze Grounding Rod Clamp for demanding applications including direct burial, where the simple mechanical design and reliable clamping power of the screw outperform other options. The GRC-34 Grounding Rod Clamp fits grounding rod with a diameter of 3/4" and rebar with a diameter of 5/8" with room to tighten the clamping screw onto a range of 10 AWG solid to 1 AWG stranded conductors. GRC-family clamps with the -SB suffix have a body and screw made from silicon
Product Type	Ground Rod Connector 3/4"
Special Features	3/4 Ground Rod Clamp - Stainless Steel Hardware

Manufacturer Information

Brand	NSi
GTIN	00662381010537
Manufacturers Part Number	GRC-34
UPC	662381010537

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Ground Rod Clamps Standard Duty

Packaging

Carton	1
Package	20
Weight Per each	0.118



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Grounding Wire
standard	cULus