



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



H100X044H1C 1/4X1 HTSHRNK LBL, 100/Cass *Panduit Corporation*

Catalog Number	H100X044H1C
Manufacturer	Panduit Corporation
Description	The H100X044H1C Military-Grade Polyolefin Die-Cut Heat-Shrink Label Cassette Contains An Integrated Memory Device For Automatic Formatting, Recall Of Last Legend Used, and The Number Of Labels Remaining In The Cassette. Compatible With Easy-Mark Plus™ Labeling Software. For Use With LS8E and LS8EQ Printers. Shrink Ratio 3:1. 1" X 0.44" (25.4 MM X 11.2 MM) Cable Diameter 0.08" - 0.25" (2 MM - 6.4 MM) Color White. 1 Cassette
Weight per unit	0.2950 (lbs/each)
Product Category	Markers & Marking Tapes

Features

Material	Polyolefin
media	Yes
Temperature Range	275

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Length	1
Size	1.00 x 0.44
Width	0.44

Descriptions

Description	1/4X1 HTSHRNK LBL,100/CASS
extra long description	PAN H100X044H1C P1™ Heat Shrink Lab
Long Description	The H100X044H1C Military-Grade Polyolefin Die-Cut Heat-Shrink Label Cassette contains an integrated memory device for automatic formatting, recall of last legend used, and the number of labels remaining in the cassette. Compatible with Easy-Mark Plus™ Labeling Software. For use with LS8E and LS8EQ printers. Shrink ratio 3:1. 1" x 0.44" (25.4 mm x 11.2 mm) Cable diameter 0.08" - 0.25" (2 mm - 6.4 mm) Color White. 1 cassette
Product Type	P1™ Heat Shrink Label



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	PANDUIT
GTIN	00074983010165
Manufacturers Part Number	H100X044H1C
UPC	074983010165

Taxonomies, Classifications, and Categories

Category Description	WIRE LUBE, MARKERS, & TIES
Type	Heat Shrink Label

Packaging

Carton	1
Package	10
Weight Per each	0.295

Uses, Certifications, and Standards

standard	MIL-M-81531 and MIL-STD-202G Method 215K, Solution A, C, and D. UL Standard 224 for flammability.
----------	---