



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## GRP14120 14" 120LB Natural CBL Tie

*Nsi Industries*

Catalog Number	GRP14120
Manufacturer	Nsi Industries
Description	The Powergrp GRP-14120 100-Count Resealable Pack Of Type 21S Ah-2 Natural-Colored Heavy-Duty Cable Ties Are 14" Long, With 120LB Of Tensile Strength For Professional Applications. They're Made From Polyamide 6, 6 Nylon, Resulting In A High Mechanical Strength and A Wide Temperature Range (-40 F to 185 F). Fasten These 14" Cables Ties Around A Wide Range Of Equipment With A Bundle Diameter Between .28" (7MM) to 4.02" (102MM), Using The Bent Tips and Serrated Locking Mechanism to Form An Effortless and
Weight per unit	0.8800 (lbs/each)
Product Category	Tools & Testers

### Features

Warranty	1 YEAR
----------	--------

### Material, Color, and Finish

Finish	Natural
--------	---------

### Descriptions

Description	14" 120LB NATURAL CBL TIE
extra long description	NSI GRP-14120 PowerGRP Cbl Tie Natu
Features	PowerGRP cable ties are a comprehensive product line of specialty ties, strong enough to handle industrial environments and ideally suited for demanding applications. The GRP-14120 ties combine a self-locking design with an industrial strength 120lb tensile strength rating, guaranteeing that these ties won't break easily. The GRP in our name stands for Guaranteed Rugged and Powerful, just one way we show that we're fully committed to building strong ties for professional users. GRP-14120 ties are water
Long Description	The PowerGRP GRP-14120 100-Count Resealable Pack of Type 21S AH-2 Natural-Colored Heavy-Duty Cable Ties are 14" long, with 120lb of tensile strength for professional applications. They're made from polyamide 6,6 nylon, resulting in a high mechanical strength and a wide temperature range (-40 F to 185 F). Fasten these 14" cables ties around a wide range of equipment with a bundle diameter between .28" (7mm) to 4.02" (102mm), using the bent tips and serrated locking mechanism to form an effortless and
Product Type	Powergrp CBL Tie Natural 14" 120LB (100PK)



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	NSi
GTIN	00662381009357
Manufacturers Part Number	GRP-14120
UPC	662381009357

## Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
----------------------	--

## Availability

minimum qty	100
-------------	-----

## Packaging

Carton	1
Package	100
Weight Per each	0.88

## Uses, Certifications, and Standards

standard	UL62275
Temperature Rating	-40F to 185F