



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL2625SW LKG WT S/SHRD FLG-Inlt, 30A 250V, L6-30P *Hubbell Wiring Devices*

Catalog Number	HBL2625SW
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Watertight Safety-Shroud® Flanged Inlet, 30A, 250V Ac, 2 Pole, 3 Wire Grounding, Nema L6-30P, Gray Valox® Housing and Flange
Weight per unit	0.5500 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	30
connection	Screw Terminals
Current Rating	30
Dielectric Strength	Withstands 2,000V minimum
insulation	Insulated Body
Number of Wires	3-Wire
pallet quantity	1000
Phase	1
Poles	2-Pole
Voltage Rating	250 V
Wattage	7,500
Wire Size	#16 to #8

Dimensions and Weight

Size	3.75 in x 3.75 in x 2.27 in
------	-----------------------------

Descriptions

Description	LKG WT S/SHRD FLG-INLT, 30A 250V, L6-30P
extra long description	HWDK HBL2625SW LKG WT S/SHRD FLG-IN
Long Description	Locking Devices, Twist-Lock®, Watertight Safety-Shroud® Flanged Inlet, 30A, 250V AC, 2 Pole, 3 Wire Grounding, NEMA L6-30P, Gray Valox® housing and flange
Product Type	LKG WT S/SHRD FLG-Inlt, 30A 250V, L6-30P
Special Features	Shrouded Watertight Construction

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585231723
Manufacturers Part Number	HBL2625SW
UPC	783585231723



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Flanged Inlet

Packaging

Carton	1
Package	5
Weight Per each	0.55

Uses, Certifications, and Standards

Application	Extra Heavy Duty Industrial
environmental conditions	Watertight
Mounting	Screw Mount
nema rating	L6-30P
standard	UL Listed, CSA Certified To Type 4, 4X And Type 12