



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL53620WSA Dup SPD RCPT, 20A 125V, 5-20R, Ow, Alarm *Hubbell Wiring Devices*

Catalog Number	HBL53620WSA
Manufacturer	Hubbell Wiring Devices
Description	TVSS Duplex Receptacle With Light and Alarm, 20A 125V, 5-20R, Office White
Weight per unit	0.3000 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
class	Normal and Common Mode
connection	Terminal Screws
Current Rating	20
Material	COMPOSITE
Outlet	STRAIGHT BLADE
Phase	1
Response Time	5
type of indicators	LED and Audible Alarm
Voltage Rating	125

Dimensions and Weight

Size	Standard
------	----------

Descriptions

Description	DUP SPD RCPT, 20A 125V, 5-20R, OW, ALARM
extra long description	HWDK HBL53620WSA DUP SPD RCPT, 20A
Features	Hubbell offers a broad range SPD receptacles with technology that is unsurpassed. Inside Hubbell SPD receptacles are two 22mm square MOVs providing 240 joules of surge protection for each mode. The nylon component shield protects the printed circuit board from contaminants. An all-glass, conformally coated PC board provides superior moisture immunity for longer life in humid environments.
Long Description	TVSS Duplex Receptacle with Light and Alarm, 20A 125V, 5-20R, Office White
Product Type	Dup SPD RCPT, 20A 125V, 5-20R, Ow, Alarm
Special Features	Standard Product



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585060293
Manufacturers Part Number	HBL5362OWSA
series	Specification Grade
UPC	783585060293

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	DUPLEX

Packaging

Carton	10
Package	1
Weight Per each	0.3

Uses, Certifications, and Standards

Application	Decorator Duplex with Light and Alarm
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Mounting Screws
standard	CSA Certified to Specification C22.2 No. 42;Listed to UL Standards 498;UL Listed File E2186