



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL8300GY Dup RCPT, HG, 20A 125V, 5-20R, Gy *Hubbell Wiring Devices*

| | |
|------------------|--|
| Catalog Number | HBL8300GY |
| Manufacturer | Hubbell Wiring Devices |
| Description | Straight Blade Devices, Receptacles, Duplex, Hospital Grade, 2-POLE3-Wire Grounding, 20A 125V, 5-20R, Gray, Single Pack. |
| Weight per unit | 0.0860 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|-------------------------------------|
| amperage rating | 20 |
| connection | Back and Side Wired Screw Terminals |
| Current Rating | 20 |
| Dielectric Strength | Withstands 2,000V minimum |
| Number of Wires | 3-Wire |
| pallet quantity | 4500 |
| Phase | 1 |
| Poles | 2-Pole |
| Voltage Rating | 125 V |
| Wattage | 2500 |
| Wire Size | #12 to #10 |

Dimensions and Weight

| | |
|------|-----------------------------|
| Size | 3.28 in x 1.65 in x 1.19 in |
|------|-----------------------------|

Descriptions

| | |
|------------------------|--|
| Description | DUP RCPT, HG, 20A 125V, 5-20R, GY |
| extra long description | HWDK HBL8300GY DUP RCPT, HG, 20A 12 |
| Features | HBL® Extra Heavy Duty Max Hospital Grade Devices - UL requirements for Hospital Grade devices is more stringent than those for standard devices. Hubbell receptacles are designed to meet and exceed the standards with Exclusive nickel-plated bypass contact design increases contact pressure, lowering the operating temperature; Four point grounding system provides redundant grounding for low resistance ground continuity in high abuse areas; Impact resistant deep face design prevents breakage. Because of these |
| Long Description | Straight Blade Devices, Receptacles, Duplex, Hospital Grade, 2-Pole3-Wire Grounding, 20A 125V, 5-20R, Gray, Single Pack. |
| Product Type | Dup RCPT, HG, 20A 125V, 5-20R, Gy |
| Special Features | Self Grounding |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|-----------------------|
| Brand | WIRING DEVICE-KELLEMS |
| GTIN | 00783585435749 |
| Manufacturers Part Number | HBL8300GY |
| series | Hospital Grade |
| UPC | 783585435749 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | Industrial receptacles |
| Type | RECEPTACLE |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.086 |

Uses, Certifications, and Standards

| | |
|--------------------------|--|
| Application | Extra Heavy Duty Hospital Grade |
| environmental conditions | Indoor Dry unless protected by additional means |
| Mounting | Screw Mount |
| nema rating | 5-20R |
| standard | CSA Certified, C22.2, No. 42 File 285;Fed. Spec. W-C-596;NEMA® WD-6 Compliant;UL Listed to UL498 File No. E2186 |