



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GUV2025 U Bolt Ground Clamp

Abb Installation Products, Inc

Catalog Number	GUV2025
Manufacturer	Abb Installation Products, Inc
Description	U-Bolt Copper Ground Clamp, Stainless Steel U-Bolt, Wire Range 2/0 - 250, Rod Size 2 to 2-3/8 Inches, Ips Pipe Size Max 2 Inches, Length 4-7/16 Inches, Width 3-11/16 Inches, Depth 1-9/16 Inches
Weight per unit	1.1 (lbs/each)
Product Category	Ground Rods & Grounding System

Features

Conductor Size	2/0 AWG - 250 kcmil
insulation	None

Material, Color, and Finish

Conductor Material	Copper
--------------------	--------

Dimensions and Weight

Length	4-7/16 in
--------	-----------

Descriptions

Description	U BOLT GROUND CLAMP
extra long description	ABB GUV2025 U BOLT GROUND CLAMP 250
Long Description	U-Bolt Copper Ground Clamp, Stainless Steel U-Bolt, Wire Range 2/0 - 250, Rod Size 2 to 2-3/8 Inches, IPS Pipe Size Max 2 Inches, Length 4-7/16 Inches, Width 3-11/16 Inches, Depth 1-9/16 Inches
Product Type	U Bolt Ground Clamp 250-2/0
Special Features	Excellent for connecting copper or copper-clad steel grounding conductor to ground rod or pipe. Specially designed spacer provides proper alignment between cable and electrode and affords more positive contact area

Manufacturer Information

Brand	Blackburn Grounding
GTIN	00783786803668
Manufacturers Part Number	GUV2025
UPC	783786803668

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GROUND CLAMP



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	3
Package	30
Weight Per each	1.09

Uses, Certifications, and Standards

standard	UL E3060, CSA 12798
----------	---------------------