



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL8452C Plug, Ang, 3P4W, 50A 3PH 250V, 15-50P, BK *Hubbell Wiring Devices*

Catalog Number	HBL8452C
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Plug, Industrial Grade, 3-Pole 4-Wire Grounding, 50A 3 Phase 250V Ac, 15-50P, Black, Single Pack.
Weight per unit	0.3940 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	50
connection	Screwed Terminal
Cord Type	All Portable
Current Rating	50
Material	COMPOSITE
Number of Wires	4-Wire
pallet quantity	765
Phase	3
Poles	3-Pole
Voltage Rating	250
Wattage	12500
Wire Size	#12 to #4

Dimensions and Weight

Size	Standard Sized
------	----------------

Descriptions

Description	PLUG,ANG,3P4W, 50A 3PH 250V,15-50P,BK
extra long description	HWDK HBL8452C PLUG,ANG,3P4W, 50A 3P
Long Description	Straight Blade Devices, Plug,Industrial Grade, 3-Pole 4-Wire Grounding, 50A 3 Phase 250V AC, 15-50P, Black, Single Pack.
Product Type	Plug, Ang, 3P4W, 50A 3PH 250V, 15-50P, BK
Special Features	Angled, 4-Position

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585015170
Manufacturers Part Number	HBL8452C
series	Extra Heavy Duty
UPC	783585015170



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Commercial cord connectors
Type	PLUG

Packaging

Carton	1
Package	5
Weight Per each	0.394

Uses, Certifications, and Standards

Application	Industrial/Commercial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	15-50P
standard	TAA Compliant (All status valid till December 2024)