



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HJ1412HWPL2LG 13.8X11.8X6 N4X FG FLT HC *Hoffman Enclosures, Inc.*

Catalog Number	HJ1412HWPL2LG
Manufacturer	Hoffman Enclosures, Inc.
Description	Flat Cover With Latches Type 4X, 13.81X11.81X5.99, LT Gray, Fiberglass
Weight per unit	9.0 (lbs/each)
Product Category	Nema Types 4, 4X, 12 & 13

### Features

ip rating	IP66
Material	Fiberglass

### Material, Color, and Finish

Color	Light Gray
Color Code	RAL 7035
Finish	Smooth Matte
Style	No Window

### Dimensions and Weight

Depth	5.99
Height	13.81
Size	15.32x13.30x6.70 in
Width	11.81

### Descriptions

Description	13.8X11.8X6 N4X FG FLT HC
extra long description	NVENT HOF HJ1412HWPL2LG TYPE 4X, FL
Features	Enclosures feature a flat, overlapping cover design that ensures a more-secure seal. Available with solid and window covers. Latches provide easy access and security.
Long Description	Flat Cover with Latches Type 4X, 13.81x11.81x5.99, Lt Gray, Fiberglass
Product Type	Type 4X, Flat HNG Latch CVR
Short Description	TYPE 4X, FLAT HNG LATCH CVR

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510158880
Manufacturers Part Number	HJ1412HWPL2LG
UPC	783510158880

### Taxonomies, Classifications, and Categories

Category Description	VYNCKIER FIBERGLASS ENCLOSURES
Type	Fiberglass and Thermoplastic Wall Mounted Industrial Enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

Status ..... Inactive .....

## Packaging

Carton ..... 1 .....

Weight Per each ..... 9 .....

## Uses, Certifications, and Standards

Application ..... Corrosive Environments; Controls and Drives .....

nema rating ..... 4X Watertight, corrosion-resistant .....