



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL5963VBK Valise Conn, 15A 125V, 5-15R, Insul-D, BK *Hubbell Wiring Devices*

Catalog Number	HBL5963VBK
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 125V , 15A 5-15R, Black, Single Pack.
Weight per unit	0.1000 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	15
connection	Screw Terminals
Current Rating	15
insulation	Insulated Body
Material	Nylon
Number of Conductors	3
Poles	2-Pole
Voltage Rating	125

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Size	Standard
------	----------

Descriptions

Description	VALISE CONN, 15A 125V, 5-15R, INSUL-D,BK
extra long description	HWDK HBL5963VBK VALISE CONN, 15A 12
Long Description	Straight Blade Devices, Female Connector Body, Valise Series, Industrial/Commercial Grade, Straight, 2-Pole 3- Wire Grounding, 125V , 15A 5-15R, Black, Single Pack.
Product Type	Valise Conn, 15A 125V, 5-15R, Insul-D, BK
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585019680
Manufacturers Part Number	HBL5963VBK
series	Valise®
UPC	783585019680

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Connector Body



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.1

Uses, Certifications, and Standards

Application	Industrial/Commercial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	5-15R
standard	CSA Certified to C22.2 No. 42 File 280C;NEMA® WD-6 Compliant;UL Listed to UL498 File E1706