



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HKD3400 HKD BRKR Complete 3P 400A 600VAC Max 65KAIC @ 480V

Eaton Corp

Catalog Number	HKD3400
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, K-Frame, HKD, Fixed Thermal, Fixed Magnetic Trip, Three-Pole, 400 A, 600 Vac, 250 VDC, 100 Kaic At 240 Vac, 65 Kaic At 480 Vac, Aluminum, Line and Load, 50/60 HZ
Weight per unit	8.0 (lbs/each)
Product Category	3 Pole Interchangeable Trip TH

### Features

Current Rating	400 A
dimensions	4.1000 IN X 5.5000 IN X 5.5000 IN
media	Yes
Poles	3
Trip Type	Fixed thermal, fixed magnetic
Voltage Rating	600 VAC, 250 VDC

### Descriptions

Description	HKD BRKR COMPLETE 3P 400A 600VAC MAX 65KAIC @ 480V
extra long description	ETN HKD3400 HKD CB COMP. 3P 400A 60
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, K-frame, HKD, Fixed thermal, Fixed magnetic trip, Three-pole, 400 A, 600 Vac, 250 Vdc, 100 kAIC at 240 Vac, 65 kAIC at 480 Vac, Aluminum, Line and load, 50/60 Hz
Product Type	HKD CB Comp. 3P 400A 600VAC Max 65kaic

### Manufacturer Information

Brand	Eaton Corp
GTIN	00786679319420
Manufacturers Part Number	HKD3400
UPC	786679319420

### Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	8

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Frequency Rating	50 to 60 Hz
standard	UL Listed