



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HLS6099301EWH6BP 6" 15W Led Disk Light 30K 90CRI 120V 900LM 6 Pack

*Cooper Lighting Solutions*

Catalog Number	HLS6099301EWH6BP
Manufacturer	Cooper Lighting Solutions
Description	6" Led Surface Light, 900 Lumens (Nominal), 90 Cri Minimum, 3000K CCT, 120V 60HZ, Le and Te Phase, Matte White Flange Cut 10 Percent Dimming, Qty 6 Bulk Pack (Not For Individual Sale)
Weight per unit	3.9 (lbs/each)
Product Category	Lighting

### Features

amperage rating	0.128A
Lamp Type	LED
Socket Type	N/A
Voltage Rating	120V
Wattage	15.4 W

### Material, Color, and Finish

Finish	Matte White
Style	(blank)

### Descriptions

Description	6" 15W LED DISK LIGHT 30K 90CRI 120V 900LM 6 PACK
extra long description	CLS HLS6099301EWH-6BP HLS, 6IN, 900
Long Description	6" LED surface light, 900 lumens (nominal), 90 CRI minimum, 3000K CCT, 120V 60Hz, LE and TE phase, matte white flange cut 10 percent dimming, Qty 6 bulk pack (not for individual sale)
Product Type	HLS, 6IN, 900LM, 3000K, Wet, 6PK
Special Features	Sizes include 4", 6", & 9"

### Manufacturer Information

Brand	HALO
GTIN	00080083256785
Manufacturers Part Number	HLS6099301EWH-6BP
UPC	080083256785

### Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	HLS Round LED Surface Mount

### Availability

Status	Inactive
--------	----------

### Packaging

Carton	1
Weight Per each	3.94



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	lighting
Mounting	Surface Mount
standard	Energy Star;IECC Compliant;UL Listed;Title 24 Compliant;RoHS Compliant