



Powering Business Worldwide

pe.eaton.com

Eaton house panel

HP816P400BSL

UPC:782116080250

Dimensions:

- **Height:** 44 IN
- **Length:** 6 IN
- **Width:** 29.75 IN

Weight:160 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 300A
- **Bus Material:** Aluminum
- **Bypass:** Lever
- **Enclosure:** NEMA 3R
- **Feed Type:** Top/bottom
- **Interrupt Rating:** 22 kAIC
- **Line:** Lug landings for compression, lugs not included
- **Main Circuit Breaker:** CSR2150
- **Mounting:** Surface
- **Number Of Circuits:** 16
- **Number Of Sockets:** 1
- **Number Of Spaces:** 8
- **Secondary Circuit Breaker:** BW/BWH
- **Security:** Ring
- **Used With:** Type BR breakers
- **Voltage Rating:** 120/240V

Supporting documents:

- [Dimensional Drawing - METER BREAKER HP816P400BSL\(BL\)](#)



- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - HP816P400BSL](#)

Certifications:

- UL Listed

Product compliance:

- EUSERC Approved

© 2016 Eaton. All rights reserved.



Powering Business Worldwide

pe.eaton.com

Eaton house panel

HP816P400BSL

UPC:782116080250

Dimensions:

- **Height:** 44 IN
- **Length:** 6 IN
- **Width:** 29.75 IN

Weight:160 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 300A
- **Bus Material:** Aluminum
- **Bypass:** Lever
- **Enclosure:** NEMA 3R
- **Feed Type:** Top/bottom
- **Interrupt Rating:** 22 kAIC
- **Line:** Lug landings for compression, lugs not included
- **Main Circuit Breaker:** CSR2150
- **Mounting:** Surface
- **Number Of Circuits:** 16
- **Number Of Sockets:** 1
- **Number Of Spaces:** 8
- **Secondary Circuit Breaker:** BW/BWH
- **Security:** Ring
- **Used With:** Type BR breakers
- **Voltage Rating:** 120/240V

Supporting documents:

- [Dimensional Drawing - METER BREAKER HP816P400BSL\(BL\)](#)



- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - HP816P400BSL](#)

Certifications:

- UL Listed

Product compliance:

- EUSERC Approved

© 2016 Eaton. All rights reserved.