



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HUB250A 2-1/2" Alu Conduit Hub

Appleton/Oz Gedney

| | |
|------------------|---|
| Catalog Number | HUB250A |
| Manufacturer | Appleton/Oz Gedney |
| Description | Appleton, Aluminum Die Cast, Watertight Hubs, Insulated and Gasketed, Unique Profile Permits Easy Wrenching. Smooth, Accurately Tapped Threads Facilitate Installation. Corrosion Resistant. Nema Types: 2, 3, 3R, 4, 4X, 12, 13. Used to Connect Rigid Metal Conduit or Imc to A Threqadless Opening In An Enclosure. Ul Standard: 514B, Ul Listed: E14814, E24264. E11853, Csa Standard: C22.2 No. 18.3. Csa Certified: 065178, Nema: FB-1, Trade Size 2.5 In |
| Weight per unit | 0.6500 (lbs/each) |
| Product Category | Aluminum |

Features

| | |
|------------------|---|
| Insulation Class | Insulated throat rated up to 105 degree C |
| Material | Body and Nut: Cooper-free Aluminum Die Cast, O-Ring: BUNA-N, Insulator: polypropylene |

Material, Color, and Finish

| | |
|--------|------------|
| Color | Grey |
| Finish | Unfinished |

Dimensions and Weight

| | |
|------|-----|
| Size | 2.5 |
|------|-----|

Descriptions

| | |
|------------------------|--|
| Description | 2-1/2" ALU CONDUIT HUB |
| extra long description | APP HUB250A 2-1/2 ALUMINUM WATERTIG |
| Long Description | Appleton, Aluminum Die Cast, Watertight Hubs, Insulated and Gasketed, Unique profile permits easy wrenching. Smooth, accurately tapped threads facilitate installation. Corrosion resistant. NEMA Types: 2,3,3R,4,4X,12, 13. Used to connect rigid metal conduit or IMC to a threqadless opening in an enclosure. UL Standard: 514B, UL Listed: E14814, E24264. E11853, CSA Standard: C22.2 No. 18.3. CSA Certified: 065178, NEMA: FB-1, Trade Size 2.5 IN |
| Product Type | 2-1/2 Aluminum Watertight Hub |
| Special Features | Unique profile permits easy wrenching. Smooth, accurately tapped threads facilitate installation. Watertight and corrosion resistant. NEMA Types: 2,3,3R,4,4X,12, 13 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Appleton |
| GTIN | 00781381430272 |
| Manufacturers Part Number | HUB250A |
| UPC | 781381430272 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS AND THREADLESS CONNECTOR |
| Type | Aluminum Die Cast, Watertight Hubs, Insulated and Gasketed |

Packaging

| | |
|-----------------|------|
| Carton | 10 |
| Weight Per each | 0.65 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Used to connect rigid metal conduit or IMC to a threadless opening in an enclosure. |
| standard | UL Standard: 514B, UL Listed: E14814, E24264. E11853, CSA Standard: C22.2 No. 18.3. CSA Certified: 065178, NEMA: FB-1 |