



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HSTT100485C HT Shrink Tubing *Panduit Corporation*

| | |
|------------------|---|
| Catalog Number | HSTT100485C |
| Manufacturer | Panduit Corporation |
| Description | Thin Wall Heat Shrink, 1" (25.4MM) Diameter, Clear Cross-Linked Polyolefin, 5 PC. Package Quantity. |
| Weight per unit | 1.4 (lbs/each) |
| Product Category | Insulating Materials |

Features

| | |
|---------------------------------|-----|
| continuous operating temperatur | 275 |
| flammability | N/A |
| Inside Diameter | 0.5 |
| media | Yes |
| outside diameter | 1 |
| Shrink Ratio | 2:1 |

Material, Color, and Finish

| | |
|-------|-----------|
| Color | Colorless |
|-------|-----------|

Dimensions and Weight

| | |
|-----------|-------|
| Thickness | 0.035 |
|-----------|-------|

Descriptions

| | |
|------------------------|---|
| Description | HT SHRINK TUBING |
| extra long description | PAN HSTT100-48-5C Dry-Shrink™ HSTT1 |
| Long Description | Thin wall heat shrink, 1" (25.4mm) diameter, clear cross-linked polyolefin, 5 pc. package quantity. |
| Product Type | Dry-Shrink™ HSTT100-48-5C Heat Shrink |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983906666 |
| Manufacturers Part Number | HSTT100-48-5C |
| UPC | 074983906666 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | HEAT/COLD SHRINK |
| Type | Heat-Shrink Tubing |

Packaging

| | |
|-----------------|------|
| Carton | 5 |
| Weight Per each | 1.35 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------------|---|
| Application | For Dry Locations |
| standard | UL Recognized, CSA Approved, MIL SPEC |