



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ICFX10WHX WHT Corner FTG *Panduit Corporation*

Catalog Number	ICFX10WHX
Manufacturer	Panduit Corporation
Description	The Power Rated Inside Corner Fitting Is Used to Efficiently Run Cables Along An Inside Corner While Maintaining A 1 Inch Bend Radius. It Is Designed to Be Used With The LDPH10 Raceway and Features A Snap-On Installation. It Meets Tia/Eia Standards, Is UL5A Listed, and Is Ul Compliant. It Is Made Of Abs Plastic and Is White.
Weight per unit	1.0 (lbs/each)
Product Category	Ducts, Raceways, Runways, Tray

Features

Cover Type	Inside Corner
Material	ABS
media	Yes

Dimensions and Weight

Length	2.49
Width	1.62

Descriptions

Description	WHT CORNER FTG
extra long description	PAN ICFX10WH-X SURFACE RACEWAY, LDP
Long Description	The power rated inside corner fitting is used to efficiently run cables along an inside corner while maintaining a 1 inch bend radius. It is designed to be used with the LDPH10 raceway and features a snap-on installation. It meets TIA/EIA Standards, is UL5A Listed, and is UL Compliant. It is made of ABS plastic and is white.
Product Type	Surface Raceway, LDPH10 Power Rated Inside Corner, White

Manufacturer Information

Brand	PANDUIT
GTIN	00074983530670
Manufacturers Part Number	ICFX10WH-X
UPC	074983530670

Taxonomies, Classifications, and Categories

Category Description	Panduit & Wiremold Metallic & Non-Metallic Raceways
Type	Power Rated Fitting



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Weight Per each	1

Uses, Certifications, and Standards

Application	Pan-Way [®] LD Surface Raceways are designed to provide easy and economical solutions for routing any low voltage cable along smooth and clean perimeter walls, baseboards or ceilings. This raceway is a perfect solution for schools, hospitals, offices, homes
standard	UI94V-0, Ft4, Meets TIA/EIA Standards, UL5A Listed, UL Compliant.