



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **IG2510 LKG RCPT, Ig, 20A 120/208V, L21-20R, or** *Hubbell Wiring Devices*

Catalog Number	IG2510
Manufacturer	Hubbell Wiring Devices
Description	Twist-Lock® Devices, Single Flush Receptacle 20A, 3 Phase Y 120/208V Ac, 4 Pole, 5 Wire Grounding, Nema L21-20R, Isolated Ground, Nylon, Orange
Weight per unit	0.3000 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
connection	Screw Terminals
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Material	Nylon
Number of Wires	5-Wire Grounding
Phase	3
Poles	4-Pole
Voltage Rating	120 V;208 V
Wattage	4,160
Wire Size	#16 to #8

### Dimensions and Weight

Size	3.28 in x 1.70 in x 1.23 in
------	-----------------------------

### Descriptions

Description	LKG RCPT, IG, 20A 120/208V, L21-20R, OR
extra long description	HWDK IG2510 LKG RCPT, IG, 20A 120/2
Features	In February 1968, Hubbell patented the first isolated ground receptacle. Today - when a clean, noise-free ground is more important than ever—Hubbell is still setting the standard. Hubbell uses insulation barrier construction on many models to isolate the ground contacts from the mounting strap. The green grounding screw is connected directly to the grounding contacts. In this way, ground contacts are separated from the mounting strap and also from the conventional grounding system. The isolated ground circ
Long Description	Twist-Lock® Devices, Single Flush Receptacle 20A, 3 Phase Y 120/208V AC, 4 Pole, 5 Wire Grounding, NEMA L21-20R, Isolated ground, nylon, Orange
Product Type	LKG RCPT, Ig, 20A 120/208V, L21-20R, or
Special Features	Isolated Ground



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585872469
Manufacturers Part Number	IG2510
UPC	783585872469

## Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	SINGLE RECEPTACLE

## Packaging

Carton	1
Package	10
Weight Per each	0.3

## Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	21-20R
standard	Certified to CSA C22.2 No.42;Fed.Spec. W-C-596;Listed to UL 498