



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IPLG14 Insd Multi-Tap Conn

Nsi Industries

Catalog Number	IPLG14
Manufacturer	Nsi Industries
Description	The Polaris IPLG1-4 Grey Multi-Tap Single Side Entry Connector Features 4 Ports Sized For 1 - 10 Awg Class B, C or D Wires or 2 - 10 Awg Class K, M or I Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Port Is Specially Designed For Fine-Stranded Copper Wires With A Pre-Installed Tin Plated Copper Ferule That Collapses As The Screw Is Tightened to Form A Strong Connection With Fine-Stranded Wires. Removable Access Plugs Cover The Hex Screws Used to Tighten The CO
Weight per unit	0.2600 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Aluminum
Number of Conductors	4
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	(Class B,C,D) 1-10 AWG - (Class K,M,I) 2-10 AWG
Wire Type	B,C,D,K,M,I

Material, Color, and Finish

Color	Grey
Finish	Plastisol Insulated

Dimensions and Weight

Size	L=1.980 - W=1.240 - H=1.370
------	-----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	INSD MULTI-TAP CONN
extra long description	NSI IPLG1-4 POLARIS Grey Multi-Tap
Features	The Polaris IPLG1-4 4-Port Single-Side Connector provides the simplest solution for forming a secure connection between up to four fine-stranded wire conductors in applications including cable trays, troughs, wire-ways, raceways, ducts and motor junction boxes. Sized for 1 - 10 AWG wires and rated for 600V, this connector installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric strength plastisol insulation,
Long Description	The Polaris IPLG1-4 Grey Multi-Tap Single Side Entry Connector features 4 ports sized for 1 - 10 AWG Class B, C or D wires or 2 - 10 AWG Class K, M or I wires. The body is made from aluminum alloy wrapped in a layer of plastisol insulation. Each port is specially designed for fine-stranded copper wires with a pre-installed tin plated copper ferule that collapses as the screw is tightened to form a strong connection with fine-stranded wires. Removable access plugs cover the hex screws used to tighten the co
Product Type	Polaris Grey Multi-Tap 1 4 Port
Special Features	(4) 1-10 AWG Class B,C,D - (4) 2-10 AWG Class K,M,I

Manufacturer Information

Brand	Polaris
GTIN	00662381951502
Manufacturers Part Number	IPLG1-4
UPC	662381951502

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Single Sided Entry

Packaging

Carton	6
Weight Per each	0.26

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B
Temperature Rating	90 C