



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IG5352I Comm 20A Side & Back Wired Ig Dup Iv

Hubbell Wiring Devices

Catalog Number	IG5352I
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Duplex Receptacle, Isolated Ground, Commercial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Back and Side Wired
Weight per unit	0.1500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and Side Wired Screw Terminals
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Material	Nylon
Number of Wires	3-Wire
Phase	1
Poles	2-Pole
Voltage Rating	125 V
Wattage	2500
Wire Size	#12 to #10

Dimensions and Weight

Size	3.28 in x 1.57 in x 1.07 in
------	-----------------------------

Descriptions

Description	COMM 20A SIDE & BACK WIRED IG DUP IV
extra long description	HWDK IG5352I COMM 20A SIDE & BACK
Features	In February 1968, Hubbell patented the first isolated ground receptacle. Today - when a clean, noise-free ground is more important than ever—Hubbell is still setting the standard. Hubbell uses insulation barrier construction on many models to isolate the ground contacts from the mounting strap. The green grounding screw is connected directly to the grounding contacts. In this way, ground contacts are separated from the mounting strap and also from the conventional grounding system. The isolated ground circ
Long Description	Straight Blade Duplex Receptacle, Isolated Ground, Commercial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Back and Side Wired
Product Type	Comm 20A Side & Back Wired Ig Dup Iv
Special Features	Isolated Ground



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585146812
Manufacturers Part Number	IG5352I
series	Hubbell-PRO
UPC	783585146812

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Isolated Ground

Packaging

Carton	1
Package	10
Weight Per each	0.15

Uses, Certifications, and Standards

Application	Hubbell-Pro Heavy Duty
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	Certified to CSA 22.2, No. 42 File 285;Fed. Spec. W-C-596;NEMA® WD-6 Compliant;UL Listed to UL498 File No. E2186