



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IG5362GRY Duplex Recp 20A Commer Isol GRD Gy

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | IG5362GRY |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Isolated Ground Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 20A 125V |
| Weight per unit | 0.1950 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|--|
| amperage rating | 20 |
| connection | Back and side wire |
| Dielectric Strength | Withstands 2000V minimum |
| indoor/outdoor | Indoor |
| Material | Nylon |
| Number of Wires | 3 |
| Outlet Type | Commercial, Indoor |
| Poles | 2 |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | 14 - 10 |

Material, Color, and Finish

| | |
|-------|------|
| Color | Gray |
|-------|------|

Dimensions and Weight

| | |
|--------|-------|
| Height | 3.281 |
| Width | .922 |

Descriptions

| | |
|------------------------|---|
| Description | DUPLEX RECP 20A COMMER ISOL GRD GY |
| extra long description | P&S IG5362GRY RECEP DUP 20A COMMER |
| Long Description | Isolated Ground Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 20A 125V |
| Product Type | Recep Dup 20A Commer Isol GRD Gry |
| Special Features | IG symbol and Isolated Ground markings for easy identification and circuit delineation. Triple-wipe brass contacts ensure lasting, positive contact with plug blades. High-impact resistant nylon face resists impacts and scrapes. Corrosion-resistant plated steel strap. Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation. Plastic barrier isolates grounding terminal from mounting strap and metal boxes. Side and internal screw-pressure-plate back wi |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007045352 |
| Manufacturers Part Number | IG5362-GRY |
| UPC | 785007045352 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|-------|
| Carton | 10 |
| Package | 100 |
| Weight Per each | 0.195 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| nema rating | 5-20R |
| standard | CULUS, UL498, CSA C22.2 No. 42, FEDSPEC |
| Temperature Rating | -40° - 60° C |