

Wire Stripper & Long-Nose Pliers

in One!



Now with Crimper

- Crimps non-insulated connectors, lugs and terminals.



MADE IN USA

**KLEIN
TOOLS** 

For Professionals... Since 1857™

All-Purpose Pliers

JOURNEYMAN™



CUTS

STRIPS

LOOPS

SHEARS

Cuts, strips and loops
solid and stranded wire.

Long nose for grabbing and looping wire.


Induction hardened cutting knives for long life.

6-32 and 8-32 screw shearing.

Hot-riveted joint ensures smooth action and no handle wobble.

Dual material Journeyman™ handles provide better grip.

Spring loaded for self-opening action.



CRIMPS
Non-insulated connectors, lugs and terminals.

NEW!
J207-8CR

J206-8C



Cat. No.	UPC 92644+	Features	Cuts and Strips	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness
J206-8C	38002-0	Spring action	8-16 AWG solid 10-18 AWG stranded	8.375" (212 mm)	2.25" (57 mm)	1" (25 mm)	.5" (13 mm)	.5" (13 mm)	.125" (3 mm)
J207-8CR	38405-9	Crimper	10-18 AWG solid 12-20 AWG stranded						

NEW!



MADE IN USA

KLEIN TOOLS
EST. 1857
For Professionals... Since 1857™

See our complete line of Journeyman™ Pliers at
www.kleintools.com



© 2015 Klein Tools, Inc.
Lincolnshire, IL 60069
96408 Rev. 07/15 A

Wire Stripper & Long-Nose Pliers

in One!



Now with Crimper

- Crimps non-insulated connectors, lugs and terminals.



MADE IN USA

KLEIN TOOLS 

For Professionals... Since 1857™

All-Purpose Pliers

JOURNEYMAN™



CUTS

STRIPS

LOOPS

SHEARS

Cuts, strips and loops
solid and stranded wire.

Long nose for grabbing and looping wire.


Induction hardened cutting knives for long life.

6-32 and 8-32 screw shearing.

Hot-riveted joint ensures smooth action and no handle wobble.

Dual material Journeyman™ handles provide better grip.

Spring loaded for self-opening action.



NEW!
J207-8CR

J206-8C



Cat. No.	UPC 92644+	Features	Cuts and Strips	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness
J206-8C	38002-0	Spring action	8-16 AWG solid 10-18 AWG stranded	8.375" (212 mm)	2.25" (57 mm)	1" (25 mm)	.5" (13 mm)	.5" (13 mm)	.125" (3 mm)
J207-8CR	38405-9	Crimper	10-18 AWG solid 12-20 AWG stranded						

NEW!



KLEIN TOOLS
EST. 1857
For Professionals... Since 1857™

See our complete line of Journeyman™ Pliers at
www.kleintools.com



© 2015 Klein Tools, Inc.
Lincolnshire, IL 60069
96408 Rev. 07/15 A