



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



JEBL18L40K80CRIW *Delisted* 135W Led RND Hbay 18000LM 4K Ip65 *Lithonia Lighting - Acuity*

| | |
|------------------|--|
| Catalog Number | JEBL18L40K80CRIW |
| Manufacturer | Lithonia Lighting - Acuity |
| Description | This Low-Profile, Entry-Level High Bay Comes Standard With Features Not Found In Comparable Competitor Product Such As Die-Cast Aluminum Construction, Quick-Disconnect Driver Housing and 6KV Surge Protection Making Jebl Extremely Durable Giving Building Owners Peace Of Mind and It'S Easy to Install, With Mounting and Reflector Options, The Jebl High Bay Can Be Used In Multiple Indoor and Outdoor Applications. |
| Weight per unit | 9.7 (lbs/each) |
| Product Category | Led Highbay Lighting |

Features

| | |
|-----------------|--------------|
| average life | 54 |
| dimensions | 13 x 13 x 5 |
| Fixture Type | HIGH BAY |
| Hardware | No |
| Lamp Included | Yes |
| Lamp Type | LED - Static |
| lumens | 18,000 |
| Material | Aluminum |
| media | Yes |
| pallet quantity | 45 |
| Power Source | Hardwired |
| Shape | Round |
| Voltage Rating | 120-277 |
| Warranty | 5 |
| Wattage | 135 |

Material, Color, and Finish

| | |
|---------------|----------------|
| Color | White |
| Finish | Gloss |
| Lens Color | WHITE |
| Lens Material | Tempered Glass |
| Style | Traditional |

Dimensions and Weight

| | |
|--------|----|
| Height | 5 |
| Length | 13 |
| Width | 13 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Construction | New Construction,Remodel |
| Description | *DELISTED* 135W LED RND HBAY 18000LM 4K IP65 |
| extra long description | LITH JEBL 18L 40K 80CRI WH LED Econ |
| Features | Design Select |
| Long Description | This low-profile, entry-level high bay comes standard with features not found in comparable competitor product such as die-cast aluminum construction, quick-disconnect driver housing and 6kV surge protection making JEBL extremely durable giving building owners peace of mind and it's easy to install, with mounting and reflector options, the JEBL high bay can be used in multiple indoor and outdoor applications. |
| Product Type | High Bay |

Manufacturer Information

| | |
|---------------------------|-----------------------|
| Brand | Lithonia Lighting |
| GTIN | 00191848153895 |
| Manufacturers Part Number | JEBL 18L 40K 80CRI WH |
| UPC | 191848153895 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | LED HIGHBAY, LOWBAY & INDUSTRIAL LIGHTING |
| Type | HIGH BAY |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 9.7 |

Uses, Certifications, and Standards

| | |
|--------------------------|--------------------------------|
| Application | Manufacturing,Warehouses |
| environmental conditions | Indoor |
| Mounting | Pendant,Suspended |
| standard | cUL,ULDLC Premium,DLC Standard |