



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



JGE3200FAG 3P 200A 25KA Fix Therm/Adj Mag BRKR W/ L/L Steel C

Eaton Corp

Catalog Number	JGE3200FAG
Manufacturer	Eaton Corp
Description	Eaton Series G Molded Case Circuit Breaker, JG-Frame, JG, Fixed Thermal, Adjustable Magnetic Trip, Three-Pole, 200 A, 600 Vac, 65 Kaic At 240 Vac, 25 Kaic At 480 Vac, 18 Kaic At 600 Vac, Line and Load, Metric, 50/60 HZ, 80% Rated
Weight per unit	6.0 (lbs/each)
Product Category	3 Pole Interchangeable Trip TH

Features

Current Rating	200 A
dimensions	3.5700 IN X 4.1300 IN X 4.1300 IN
frame	JG
interrupt rating	18 kAIC at 600 Vac65 kAIC at 240 Vac25 kAIC at 480 Vac
media	Yes
Poles	3
Trip Type	Fixed thermal, adjustable magnetic
Voltage Rating	600 VAC

Descriptions

Description	3P 200A 25KA FIX THERM/ADJ MAG BRKR W/ L/L STEEL C
extra long description	ETN JGE3200FAG 3P 200A 25KA Fix The
Features	The Eaton Series G Molded Case Circuit Breaker provides users with unparalleled performance and convenience. A patented contact design features high-speed "blow-open" action, resulting in superior circuit breaker performance. This globally-rated platform offers users high interruption ratings in a compact footprint with ease of in-field configuration applicable to a wide variety of industry and regional requirements. Choose from a selection of thermal magnetic and electronic trip units, available in curren
Long Description	Eaton Series G molded case circuit breaker, JG-frame, JG, Fixed thermal, adjustable magnetic trip, Three-pole, 200 A, 600 Vac, 65 kAIC at 240 Vac, 25 kAIC at 480 Vac, 18 kAIC at 600 Vac, Line and load, Metric, 50/60 Hz, 80% rated
Product Type	3P 200A 25KA Fix Therm/Adj Mag CB W/L/L



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Eaton
GTIN	00782113526720
Manufacturers Part Number	JGE3200FAG
UPC	782113526720

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker

Packaging

Carton	1
Weight Per each	6

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Frequency Rating	50 to 60 Hz
standard	CSA Certified, IEC Rated, UL Listed, CE Marked