



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KL221 A:4, B:4 Alu Comp Splice

Abb Installation Products, Inc

Catalog Number	KL221
Manufacturer	Abb Installation Products, Inc
Description	Aluminum 3-1/2 Inch Service Entrance Compression Splice For Wire Range - End A: 4 STR., 4 STR. Compact, Orange, End B: 4 STR., 4 STR. Compact, Orange, Die: 840. For Al to Al and Al to Cu Conductors.
Weight per unit	0.1960 (lbs/each)
Product Category	Large Terminals & Connectors

Features

connection	Compression
insulation	None
Material	Aluminum
Number of Conductors	2

Dimensions and Weight

Size	3-1/2 Inch
------	------------

Descriptions

Description	A:4,B:4 ALU COMP SPLICE
extra long description	ABB KL22-1 COMPRSLLEEVE CONNECTOR
Long Description	Aluminum 3-1/2 Inch Service Entrance Compression Splice for Wire Range - End A: 4 Str., 4 Str. Compact, Orange, End B: 4 Str., 4 Str. Compact, Orange, Die: 840. For AL to AL and AL to CU Conductors.
Product Type	Comprsleeve Connector
Special Features	Splices large conductors required for commercial service, use as low cost reducing sleeve. All sizes can be installed with popular mechanical and hydraulic tools. Center stop assures proper conductor positioning. Quick identifications with color-coded foil caps

Manufacturer Information

Brand	Blackburn Mechanical
GTIN	00783786047505
Manufacturers Part Number	KL22-1
UPC	783786047505

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Compression Splice Service Entrance



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	25
Package	250
Weight Per each	0.196

Uses, Certifications, and Standards

Application	For Combinations of Aluminum-to-Aluminum and Aluminum-to-Copper Conductors
environmental conditions	All Seasons / Conditions
Mounting	None
standard	Passes the requirements of ANSI C119.4 / Passes the requirements of ANSI C119.4