

# Specifications



## Eaton KRP-C-1200SP

Eaton Bussmann Series Class L fuse, KRP-C, time-delay, current limiting fuse, 1200 A, interrupting rating of 300 kA at 600 Vac and 100 kA at 300 Vdc

### General specifications

PRODUCT NAME	Eaton Bussmann series KRP-C fuse
CATALOG NUMBER	KRP-C-1200SP
UPC	051712605120
PRODUCT LENGTH/DEPTH	10.75 in
PRODUCT HEIGHT	2.78 in
PRODUCT WIDTH	2.78 in
PRODUCT WEIGHT	0.001 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked <a href="#">RoHS Compliant</a>

Electrical rating	
AMPERAGE RATING	1200 A
INTERRUPT RATING	300 kAIC at 600 Vac 100 kAIC Vdc
RESPONSE TIME	4 sec at 500%
VOLTAGE RATING	600 Vac, 300 Vdc

General information	
CLASS	Class L
CONNECTION	Bolted blade end x bolted blade end
FUSE INDICATOR	Non-indicating

Physical details	
PACKAGING TYPE	Standard

Resources	
CATALOGS	<a href="#">Bussmann Full Line Catalog</a>
	<a href="#">Low Voltage Branch Circuit Fuse Chapter</a>
COMPLIANCE INFORMATION	<a href="#">RoHS Search Tool</a>
MULTIMEDIA	<a href="#">Bussmann series Fuseology</a>
TECHNICAL DATA SHEETS	<a href="#">Bussmann series KRP-C 601 to 2000A Class L fuse data sheet No. 1008</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton KRP-C-1200SP

Eaton Bussmann Series Class L fuse, KRP-C, time-delay, current limiting fuse, 1200 A, interrupting rating of 300 kA at 600 Vac and 100 kA at 300 Vdc

### General specifications

PRODUCT NAME	Eaton Bussmann series KRP-C fuse
CATALOG NUMBER	KRP-C-1200SP
UPC	051712605120
PRODUCT LENGTH/DEPTH	10.75 in
PRODUCT HEIGHT	2.78 in
PRODUCT WIDTH	2.78 in
PRODUCT WEIGHT	0.001 lb
WARRANTY	Not Applicable
COMPLIANCES	CE Marked <a href="#">RoHS Compliant</a>

Electrical rating	
AMPERAGE RATING	1200 A
INTERRUPT RATING	300 kAIC at 600 Vac 100 kAIC Vdc
RESPONSE TIME	4 sec at 500%
VOLTAGE RATING	600 Vac, 300 Vdc

General information	
CLASS	Class L
CONNECTION	Bolted blade end x bolted blade end
FUSE INDICATOR	Non-indicating

Physical details	
PACKAGING TYPE	Standard

Resources	
CATALOGS	<a href="#">Bussmann Full Line Catalog</a>
	<a href="#">Low Voltage Branch Circuit Fuse Chapter</a>
COMPLIANCE INFORMATION	<a href="#">RoHS Search Tool</a>
MULTIMEDIA	<a href="#">Bussmann series Fuseology</a>
TECHNICAL DATA SHEETS	<a href="#">Bussmann series KRP-C 601 to 2000A Class L fuse data sheet No. 1008</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

