



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



K50SG 1/2" FM5 CNDT CVR & GSKT *Crouse-Hinds*

Catalog Number	K50SG
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Form 5 Integral Gasket Cover, Sheet Steel, 1/2"
Weight per unit	0.1400 (lbs/each)
Product Category	Bodies & Covers

Features

dimensions	1.3800 IN X 1.3800 IN X 0.3800 IN
Form	Form 5

Material, Color, and Finish

Finish	ELECTROGALVANIZED
--------	-------------------

Dimensions and Weight

Hub Size	1/2 in
----------	--------

Descriptions

Description	1/2" FM5 CNDT CVR & GSKT
extra long description	CRS-H K50SG 1/2 FORM 5 COVER SHEET
Features	Form 5 malleable iron conduit bodies, covers and gaskets from Eaton's Crouse-Hinds Division are used in conduit systems to act as pull outlets for conductors being installed, provide openings for making splices and taps in conductors, make 90 degree bends in conduit runs, and provide access to conductors for maintenance and future system changes. Form 5 conduit bodies are manufactured in trade sizes 1/2" to 4", and are interchangeable with Appleton Form 35 conduit bodies. They are also available with a h
Long Description	Eaton Crouse-Hinds series Condulet Form 5 integral gasket cover, Sheet steel, 1/2"
Product Type	1/2 Form 5 Cover Sheet Steel With GSKT
Special Features	With Neoprene Integral Gasket

Manufacturer Information

Brand	Crouse-Hinds
GTIN	00662277002752
Manufacturers Part Number	K50SG
UPC	662277002752

Taxonomies, Classifications, and Categories

Type	Integral gasket cover
------	-----------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	50
Weight Per each	0.14

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Enclosure standard	NEMA 4 UL 514B, CSA C22.2, CUL