



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KTK212 2-1/2A 600V Fa Midget Fuse

Bussmann Fuses

Catalog Number	KTK212
Manufacturer	Bussmann Fuses
Description	Eaton Bussmann Series KTK Fuse, Control Circuits, Lighting Circuit Protection, Meter Circuits, 2.5 A, Non-Indicating, Ferrule End X Ferrule End, 100 Kaic At 600 V, Nickel-Plated Bronze Endcap, Melamine Tube, 600 V
Weight per unit	0.0200 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	2-1/2 Amp
class	Supplemental
connection	Ferrule End X Ferrule End
dimensions	0.4100 IN X 0.4100 IN X 1.5000 IN
interrupt rating	100000 Amp (RMS Symmetrical UL)
Material	Melamine tubeNickel-plated bronze endcap
media	Yes
Voltage Rating	600 VAC

Dimensions and Weight

Size	13/32 In Diameter X 1-1/2 In Length
------	-------------------------------------

Descriptions

Description	2-1/2A 600V FA MIDGET FUSE
extra long description	BUSS KTK-2-1/2 LIMITRON FAST ACTING
Features	Bussmann offers the broadest selection of Supplemental and Midget fuses in both time-delay and fast-acting designs with voltages as high as 600Vac and 600Vdc.
Long Description	Eaton Bussmann series KTK fuse, Control circuits, Lighting circuit protection, Meter circuits, 2.5 A, Non-indicating, Ferrule end x ferrule end, 100 kAIC at 600 V, Nickel-plated bronze endcap, Melamine tube, 600 V
Product Type	Limitron Fast Acting Fuse
Special Features	Nickel Plated Bronze Endcap

Manufacturer Information

Brand	Eaton
GTIN	00051712420228
Manufacturers Part Number	KTK-2-1/2
UPC	051712420228



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description MIDGET FUSES

Type FUSE

Packaging

Carton 10

Weight Per each 0.02

Uses, Certifications, and Standards

Application Ind Facilities & Factories - Facility: Safety and Security Systems

standard CE Marked, RoHS Compliant