


# WALL PLATES, INSERTS & ENCLOSURES GUIDE



designed to be better.™





### WALLPLATES & INSERTS

Our line of Keystone wall plates and Cat 5e, Cat6, Cat6a, F-Connectors, speaker binding posts and RCA inserts provide flexible setup options at any location.

### DECORATOR STRAPS

We offer a series of pre-configured outlet straps for data, phone, video and home theater applications. Add a home theater strap to enable HD audio and video with a few simple connections, or quickly wire a home office using our pre-configured outlet straps that combine phone, data and video into a single decorator opening.

### ENCLOSURES

Our durable enclosures range in size from 12 to 42 inches to suit any installation. Every enclosure is made in the USA and is compatible with all major module mounting schemes. They offer three 2.5" top openings for high capacity projects, side lances and side tabs for more flexible installation options. Available with hinged or screw-on doors, a Legrand enclosure is the easy choice for professional projects.



# KEYSTONE INSERTS

## TELEPHONE AND DATA Keystone Inserts



WP3475-WH\*

WP3476-WH

WP346A-WH

WP3450-WH\*

WP3460-WH

WP3458-WH

WP3451-WH

WP3425-WH

WP3550-WH

WP3560-WH

\* Available in white, light almond, and blue in packs of 50

PART NO.	DESCRIPTION
WP3475-XX	Cat 5e Quick Connect RJ45 Keystone Connector Colors: BE, BK, BR, GY, GN, IV, LA, OR, RE, WH, YE <b>... CAN BE USED WITH THE LABOR SAVING PUNCH &amp; GO TOOL.</b>
WP3476-XX	Cat 6 Quick Connect RJ45 Keystone Connector Colors: BE, BK, BR, GY, IV, LA, OR, RE, WH
WP346A-XX	Cat 6a Quick Connect RJ45 Keystone Insert Colors: BE, BK, BR, GY, GN, IV, LA, OR, RE, WH, YE
WP3450-XX (KS58ABxx)†	Cat 5e RJ45 Keystone Connector Colors: BE (BL), BK, BR, GY (GRY), IV (I), LA, OR, RE (RED), WH (WH)
WP3460-XX (KS68ABxx)†	Cat 6 RJ45 Keystone Connector Colors: BE (BL), BK, BR, GY (GRY), IV (I), LA, OR, RE (RED), WH (WH)
WP3458-XX	Cat 5e Keyed RJ45 Keystone Connector Colors: BK, BR, IV, LA, WH
WP3451-XX (KS888xx)	Cat 5e RJ45 Keystone Coupler Colors: BK, WH (W)
WP3425-XX (KS6Uxx)†	RJ25 6P6C Keystone Connector Colors: BK, BR, IV (I), LA, WH (W)
WP3550-XX	Snap & Go Cat 5e Keystone Connector Colors: BE, BK, BR, GY, IV, LA, OR, RE, WH
WP3560-XX	Snap & Go Cat 6 Keystone Connector Colors: BE, BK, BR, GY, IV, LA, OR, RE, WH

## VIDEO INSERTS



WP3479-WH\*

WP3480-WH

WP3481-WH\*

WP3482-WH

WP1234-WH

WP3455-WH

KSBNCW

KSSVW


\*Available in packs of 50.

PART NO.	DESCRIPTION
WP3479-XX	Non-Recessed Coax Keystone F-Connector (1 GHz) 50 Count Bulk Pack in WH or LA (WP3479-XX-50)
WP3480-XX	Recessed Gold F-Connector (3GHz)
WP3481-XX (KSFFxx)	Recessed Nickle F-Connector (3GHz) 50 Count Bulk Pack in WH (WP3481-WH-50)
WP3482-XX (KSFFSTxx)	Recessed Self-Terminating Keystone F-Connector (1 GHz)
WP1234-XX	HDMI Keystone Insert/Coupler
WP3455-XX (KSBL10xx)†	Blank Keystone Insert Colors: BK, BR, IV (I), LA, WH (W)
KSBNCxx	Keystone BNC-to-BNC Connector
KSSVxx	Keystone S-Video-to-110 Termination Colors: I, LA, W

### COLOR OPTIONS



# WALL PLATES, INSERTS & ENCLOSURES GUIDE



designed to be better.™





### WALLPLATES & INSERTS

Our line of Keystone wall plates and Cat 5e, Cat6, Cat6a, F-Connectors, speaker binding posts and RCA inserts provide flexible setup options at any location.

### DECORATOR STRAPS

We offer a series of pre-configured outlet straps for data, phone, video and home theater applications. Add a home theater strap to enable HD audio and video with a few simple connections, or quickly wire a home office using our pre-configured outlet straps that combine phone, data and video into a single decorator opening.

### ENCLOSURES

Our durable enclosures range in size from 12 to 42 inches to suit any installation. Every enclosure is made in the USA and is compatible with all major module mounting schemes. They offer three 2.5" top openings for high capacity projects, side lances and side tabs for more flexible installation options. Available with hinged or screw-on doors, a Legrand enclosure is the easy choice for professional projects.



# KEYSTONE INSERTS

## TELEPHONE AND DATA Keystone Inserts



WP3475-WH\*



WP3476-WH



WP346A-WH



WP3450-WH\*



WP3460-WH



WP3458-WH



WP3451-WH



WP3425-WH



WP3550-WH



WP3560-WH

\* Available in white, light almond, and blue in packs of 50

PART NO.	DESCRIPTION
WP3475-XX	Cat 5e Quick Connect RJ45 Keystone Connector Colors: BE, BK, BR, GY, GN, IV, LA, OR, RE, WH, YE
	<b>... CAN BE USED WITH THE LABOR SAVING PUNCH &amp; GO TOOL.</b>
WP3476-XX	Cat 6 Quick Connect RJ45 Keystone Connector Colors: BE, BK, BR, GY, IV, LA, OR, RE, WH
WP346A-XX	Cat 6a Quick Connect RJ45 Keystone Insert Colors: BE, BK, BR, GY, GN, IV, LA, OR, RE, WH, YE
WP3450-XX (KS58ABxx) <sup>†</sup>	Cat 5e RJ45 Keystone Connector Colors: BE (BL), BK, BR, GY (GRY), IV (I), LA, OR, RE (RED), WH (WH)
WP3460-XX (KS68ABxx) <sup>†</sup>	Cat 6 RJ45 Keystone Connector Colors: BE (BL), BK, BR, GY (GRY), IV (I), LA, OR, RE (RED), WH (WH)
WP3458-XX	Cat 5e Keyed RJ45 Keystone Connector Colors: BK, BR, IV, LA, WH
WP3451-XX (KS888xx)	Cat 5e RJ45 Keystone Coupler Colors: BK, WH (W)
WP3425-XX (KS6Uxx) <sup>†</sup>	RJ25 6P6C Keystone Connector Colors: BK, BR, IV (I), LA, WH (W)
WP3550-XX	Snap & Go Cat 5e Keystone Connector Colors: BE, BK, BR, GY, IV, LA, OR, RE, WH
WP3560-XX	Snap & Go Cat 6 Keystone Connector Colors: BE, BK, BR, GY, IV, LA, OR, RE, WH


## VIDEO INSERTS




WP3479-WH\*



WP3480-WH



WP3481-WH\*



WP3482-WH



WP1234-WH



WP3455-WH



KSBNCW



KSSVW

\*Available in packs of 50.

PART NO.	DESCRIPTION
WP3479-XX	Non-Recessed Coax Keystone F-Connector (1 GHz) 50 Count Bulk Pack in WH or LA (WP3479-XX-50)
WP3480-XX	Recessed Gold F-Connector (3GHz)
WP3481-XX (KSFFxx)	Recessed Nickle F-Connector (3GHz) 50 Count Bulk Pack in WH (WP3481-WH-50)
WP3482-XX (KSFFSTxx)	Recessed Self-Terminating Keystone F-Connector (1 GHz)
WP1234-XX	HDMI Keystone Insert/Coupler
WP3455-XX (KSBL10xx) <sup>†</sup>	Blank Keystone Insert Colors: BK, BR, IV (I), LA, WH (W)
KSBNCxx	Keystone BNC-to-BNC Connector
KSSVxx	Keystone S-Video-to-110 Termination Colors: I, LA, W

## COLOR OPTIONS

