



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KTALED140M13NM85 *Delisted* 140W 9600 Lmens T3 10KV Surge PR *Keystone Technologies*

Catalog Number	KTALED140M13NM85
Manufacturer	Keystone Technologies
Description	140W Led Area Light With Nema Type 3-Pin Twist Lock Receptacle + Shorting Cap, Series 1 Medium Housing. 120-277V Input, 5000K, Type Iii Optics, 0-10V Dimmable. Standard Bronze Housing
Weight per unit	13.2 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	N/A
Circuit Type	N/A
Input Voltage	120-277V
ip rating	IP65
lumens	19600
Nominal Length	N/A
Nominal Size	Medium Housing
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	140
Wire Type	N/A

Material, Color, and Finish

Base Type	N/A
color rendering index (cri)	>80 Deg
color temperature	5000
housing color	N/A

Descriptions

Construction	N/A
Description	*DELISTED* 140W 9600 LMENS T3 10KV SURGE PR
extra long description	Key KT-ALED140-M1-3-NM-850-VDIM 14
Long Description	140W LED Area Light with NEMA Type 3-pin Twist Lock Receptacle + Shorting Cap, Series 1 Medium Housing. 120-277V Input, 5000K, Type III Optics, 0-10V Dimmable. Standard Bronze Housing
Product Type	140W, 19600 Lumens, Dist. Iii, Extra 10KV Surge Protection,



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00843654131412
Manufacturers Part Number	KT-ALED140-M1-3-NM-850-VDIM
UPC	843654131412

Taxonomies, Classifications, and Categories

Category Description	LED CANOPY, PARKING, POLE MOUNTED & ROADWAY LIGHTING
----------------------	------------------------------------------------------

Packaging

Carton	1
Weight Per each	13.23

Uses, Certifications, and Standards

Energy Star	Y
-------------	---