



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L14.5T848G8CSJDX 14.5W Led T8 48" 3K/35/4K/5K/65K SGL/DBL End-Glass *Keystone Technologies*

Catalog Number	L14.5T848G8CSJDX
Manufacturer	Keystone Technologies
Description	14.5W Led T8 Tube, 1800 Lumen, Glass Construction, 4FT, Color Select 3000/3500/4000/5000K/6500K, 120-277V Input, Direct Drive, Single and Double Ended Wiring
Weight per unit	0.0272 (lbs/each)
Product Category	Lighting

Features

Ballast Type	N/A
beam angle	220 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	Ip20
lumens	1800
Nominal Length	48 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	14.5
Wire Type	N/A

Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	Switchable: 3/3.5/4/5K
housing color	N/A

Descriptions

Construction	N/A
Description	14.5W LED T8 48" 3K/35/4K/5K/65K SGL/DBL END-GLASS
extra long description	Key KT-LED14.5T8-48G-8CSJ-DX2 14.5W
Long Description	14.5W LED T8 Tube, 1800 lumen, Glass Construction, 4ft, Color Select 3000/3500/4000/5000K/6500k, 120-277v Input, Direct Drive, Single and Double Ended Wiring
Product Type	14.5W Led T8 Tube, 1800 Lumen, Glass Construction, 4FT, Colo



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00843654154596
Manufacturers Part Number	KT-LED14.5T8-48G-8CSJ-DX2
UPC	843654154596

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	1
Package	25
Weight Per each	0.0272

Uses, Certifications, and Standards

Energy Star	N
-------------	---