



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## KTLED54T896P850D 54W Led T8 96" 50K 120-277V 6000LM

*Keystone Technologies*

Catalog Number	KTLED54T896P850D
Manufacturer	Keystone Technologies
Description	54W Led T8 Lamp, 8 Long, R17D Base, 5000K, 120-277V Input, Internal Driver. 20 PCS Carton, Individual Protective Sleeves. Direct Drive
Weight per unit	2.7 (lbs/each)
Product Category	Shape & Circular Lamps

### Features

Ballast Type	N/A
beam angle	180 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	5900
Nominal Length	96 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	54
Wire Type	N/A

### Material, Color, and Finish

Base Type	R17D
color rendering index (cri)	>80 Deg
color temperature	5000
housing color	N/A

### Descriptions

Construction	N/A
Description	54W LED T8 96" 50K 120-277V 6000LM
extra long description	Key KT-LED54T8-96P-850-D /G2-DP 54W
Long Description	54W LED T8 LAMP, 8 LONG, R17D BASE, 5000K, 120-277V INPUT, INTERNAL DRIVER. 20 PCS CARTON, INDIVIDUAL PROTECTIVE SLEEVES. DIRECT DRIVE
Product Type	54W, 6000 Lumens, 8', 120' Beam Angle, Ballast Bypass, Rec.



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Keystone
GTIN	00890949014646
Manufacturers Part Number	KT-LED54T8-96P-850-D /G2-DP
UPC	890949014646

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	------------------------------------------------------------------

## Packaging

Carton	1
Weight Per each	2.7

## Uses, Certifications, and Standards

Energy Star	N
-------------	---