



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



KTLED54T896P850D 54W Led T8 96" 50K 120-277V 6000LM

Keystone Technologies

Catalog Number	KTLED54T896P850D
Manufacturer	Keystone Technologies
Description	54W Led T8 Lamp, 8 Long, R17D Base, 5000K, 120-277V Input, Internal Driver. 20 PCS Carton, Individual Protective Sleeves. Direct Drive
Weight per unit	2.7 (lbs/each)
Product Category	Shape & Circular Lamps

Features

Ballast Type	N/A
beam angle	180 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	5900
Nominal Length	96 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	54
Wire Type	N/A

Material, Color, and Finish

Base Type	R17D
color rendering index (cri)	>80 Deg
color temperature	5000
housing color	N/A

Descriptions

Construction	N/A
Description	54W LED T8 96" 50K 120-277V 6000LM
extra long description	Key KT-LED54T8-96P-850-D /G2-DP 54W
Long Description	54W LED T8 LAMP, 8 LONG, R17D BASE, 5000K, 120-277V INPUT, INTERNAL DRIVER. 20 PCS CARTON, INDIVIDUAL PROTECTIVE SLEEVES. DIRECT DRIVE
Product Type	54W, 6000 Lumens, 8', 120' Beam Angle, Ballast Bypass, Rec.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00890949014646
Manufacturers Part Number	KT-LED54T8-96P-850-D /G2-DP
UPC	890949014646

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	1
Weight Per each	2.7

Uses, Certifications, and Standards

Energy Star	N
-------------	---