



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L18PSHIDE26850D 9/12/18W Led Hid Repl 50K Med Base 1300-2600 LM

Keystone Technologies

| | |
|------------------|---|
| Catalog Number | L18PSHIDE26850D |
| Manufacturer | Keystone Technologies |
| Description | Led Hid Replacement Lamp, Power Select 18/12/9W, E26 Base, 5000K, 120-277V Input, Directdrive |
| Weight per unit | 0.0456 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-----------------|----------|
| Ballast Type | N/A |
| beam angle | 360 Deg |
| Circuit Type | N/A |
| Input Voltage | 120-277V |
| ip rating | N/A |
| lumens | N/A |
| Nominal Length | N/A |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Wattage | 18/12/9 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | E26 |
| color rendering index (cri) | >80 Deg |
| color temperature | 5000 |
| housing color | N/A |

Descriptions

| | |
|------------------------|---|
| Construction | N/A |
| Description | 9/12/18W LED HID REPL 50K MED BASE 1300-2600 LM |
| extra long description | Key KT-LED18PSHID-E26-850-D /G4 LED |
| Long Description | LED HID Replacement Lamp, Power Select 18/12/9W, E26 Base, 5000K, 120-277V Input, DirectDrive |
| Product Type | Led Hid Replacement Lamp, Power Select 18/12/9W, E26 Base, 5 |

Manufacturer Information

| | |
|---------------------------|-----------------------------|
| Brand | Keystone |
| GTIN | 00843654138145 |
| Manufacturers Part Number | KT-LED18PSHID-E26-850-D /G4 |
| UPC | 843654138145 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description LED SPECIALTY LAMPS & MODULES

Packaging

Carton 1

Weight Per each 0.0456

Uses, Certifications, and Standards

Energy Star N