



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L25T5H048GC840DX 25W Led T5HO 48" 40K DBL/SNGL End 3400LM

Keystone Technologies

| | |
|------------------|---|
| Catalog Number | L25T5H048GC840DX |
| Manufacturer | Keystone Technologies |
| Description | 25W Led T5 Tube, Shatter-Proof Coated Glass, Direct Drive, Single or Double Ended, 4 FT., 4000K, 80+Cri, 120-277V Input |
| Weight per unit | 0.5200 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-----------------|----------|
| Ballast Type | N/A |
| beam angle | 240 Deg |
| Circuit Type | N/A |
| Input Voltage | 120-277V |
| ip rating | N/A |
| lumens | N/A |
| Nominal Length | 48 in |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Warranty | 5 |
| Wattage | 25 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | G5 |
| color rendering index (cri) | >80 Deg |
| color temperature | 4000 |
| housing color | N/A |

Descriptions

| | |
|------------------------|---|
| Construction | Frosted Shatterproof Glass |
| Description | 25W LED T5HO 48" 40K DBL/SNGL END 3400LM |
| extra long description | Key KT-LED25T5HO-48GC-840-DX2 25W, |
| Long Description | 25W LED T5 Tube, Shatter-Proof Coated Glass, Direct Drive, Single or Double Ended, 4 ft., 4000K, 80+CRI, 120-277V Input |
| Product Type | 25W, 3400 Lumen, 4', 240' Beam Angle, Ballast Bypass, DLC 4. |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|-------------------------------|
| Brand | Keystone |
| GTIN | 00843654130590 |
| Manufacturers Part Number | KT-LED25T5HO-48GC-840-DX2 /G2 |
| UPC | 843654130590 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
|----------------------|--|

Packaging

| | |
|-----------------|------|
| Carton | 25 |
| Weight Per each | 0.52 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Energy Star | N |
|-------------|---|