



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L11T836G8CSJDX2 11W Led T8 36" 3K/35K/4K/5K/65K SGL/DBL End-Glass

Keystone Technologies

| | |
|------------------|---|
| Catalog Number | L11T836G8CSJDX2 |
| Manufacturer | Keystone Technologies |
| Description | 11W Led T8 Tube, 1500 Lumen, Glass Construction, 3FT, Color Select 3000/3500/4000/5000K/6500K, 120-277V Input, Direct Drive, Single and Double Ended Wiring |
| Weight per unit | 0.0200 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-----------------|----------|
| Ballast Type | N/A |
| beam angle | 240 Deg |
| Circuit Type | N/A |
| Input Voltage | 120-277V |
| ip rating | N/A |
| lumens | 1500 |
| Nominal Length | 36 in |
| Nominal Size | N/A |
| Number of Lamps | N/A |
| Output Current | N/A |
| Output Voltage | N/A |
| Sensor Type | N/A |
| Wattage | 11 |
| Wire Type | N/A |

Material, Color, and Finish

| | |
|-----------------------------|---------|
| Base Type | G13 |
| color rendering index (cri) | >80 Deg |
| color temperature | N/A |
| housing color | N/A |

Descriptions

| | |
|------------------------|---|
| Construction | Frosted Glass |
| Description | 11W LED T8 36" 3K/35K/4K/5K/65K SGL/DBL END-GLASS |
| extra long description | Key KT-LED11T8-36G-8CSJ-DX2 11W LED |
| Long Description | 11W LED T8 Tube, 1500 lumen, Glass Construction, 3ft, Color Select 3000/3500/4000/5000K/6500k, 120-277v Input, Direct Drive, Single and Double Ended Wiring |
| Product Type | 11W Led T8 Tube, 1500 Lumen, Glass Construction, 3FT, Color |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|-------------------------|
| Brand | Keystone |
| GTIN | 00843654141435 |
| Manufacturers Part Number | KT-LED11T8-36G-8CSJ-DX2 |
| UPC | 843654141435 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS |
|----------------------|--|

Packaging

| | |
|-----------------|------|
| Carton | 25 |
| Weight Per each | 0.02 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Energy Star | N |
|-------------|---|