



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



L515C Turnlok Conn 3W 15A 125V

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | L515C |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Turnlok Registered Connector 3-Wire 15A 125a |
| Weight per unit | 0.1800 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|-----------------|-------|
| amperage rating | 15 |
| Material | Nylon |
| Number of Wires | 3.0 |
| Poles | 2 |
| Voltage Rating | 125 |
| Wire Size | 4 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Black |
|-------|-------|

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|

Descriptions

| | |
|------------------------|--|
| Description | TURNLOK CONN 3W 15A 125V |
| extra long description | P&S PSL515C TURNLOK CONN 3W 15A 125 |
| Long Description | Turnlok Registered Connector 3-Wire 15A 125A |
| Product Type | Turnlok Conn 3W 15A 125V |
| Special Features | Locking Device, impact resistant |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007236644 |
| Manufacturers Part Number | PSL515C |
| UPC | 785007236644 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------|
| Category Description | Commercial cord connectors |
| Type | Turnlock Connector |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.18 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|-----------------------|
| Application | Industrial Spec Grade |
| Mounting | Connector |
| nema rating | L5-15R |
| standard | UL 498 |