ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



L1630PW PLUG WT 30A 480V 3PH 3P4W H/L YL

EATON WIRING DEVICES

Catalog Number	L1630PW
Manufacturer	EATON WIRING DEVICES
Description	Eaton Arrow Hart watertight locking plug, #18-10 AWG, 30A, Industrial, 480V, Back, Yellow, Steel, Watertight, L16-30, Three-pole, Four-wire, Santoprene, 0.43 to 1.15 in, IP67
Weight per unit	0.8100 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

Material	Santoprene thermoplastic elastomeric
Dimensions	6.7500 IN X 4.2500 IN X 4.0000 IN

Descriptions

Description	PLUG WT 30A 480V 3PH 3P4W H/L YL
Features	Arrow Hart's broad line of straight blade watertight devices provide superior watertight protection. These versatile products are ideal for food processing plants, oil refineries or chemical processing plants — anywhere that moisture, dirt or corrosive elements may be a factor.
Long Description	Eaton Arrow Hart watertight locking plug, #18-10 AWG, 30A, Industrial, 480V, Back, Yellow, Steel, Watertight, L16-30, Three-pole, Four-wire, Santoprene, 0.43 to 1.15 in, IP67
Product Type	Plug WT 30A 480V 3PH 3P4W H/L Yl
Special Features	Watertight locking
Extra Long Description	EWD L1630PW Plug WT 30A 480V 3PH 3P

Manufacturer Information

Brand	Eaton
	COOPER WIRING DEVICES
GTIN	00040893642123
UPC	781430

Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Watertight locking plug

Packaging

Carton	1
Package	10
Weight Per Each	0.8100 (lbs/each)

2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility - Other
Standard	RoHS Compliant

Specifications







Eaton L1630PW

Eaton Arrow Hart watertight locking plug, #18-10 AWG, 30A, Industrial, 480V, Back, Yellow, Steel, Watertight, L16-30, Three-pole, Four-wire, Santoprene, 0.43 to 1.15 in, IP67

General specifications	
PRODUCT NAME	Eaton Arrow Hart watertight locking plug
CATALOG NUMBER	L1630PW
UPC	040893642123
PRODUCT LENGTH/DEPTH	6.75 in
PRODUCT HEIGHT	4 in
PRODUCT WIDTH	4.25 in
PRODUCT WEIGHT	0.81 lb
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Watertight locking plug

Electrical Ratings

AMPERAGE RATING	30A
NEMA CONFIGURATION	L16-30
NUMBER OF POLES	Three-pole
NUMBER OF WIRES	4
TORQUE RATING	20 lbf-inch
VOLTAGE RATING	480 V

Environmental Specifications

ENVIRONMENTAL RESISTANCE	Watertight

Installation Specifications

ALLOWABLE WIRE SIZE	#18-10 AWG
WIRING METHOD	Back

Material Specifications

COLOR	Yellow
CONTACT MATERIAL	Steel

Product Specifications

APPLICATION	Industrial
CORD DIAMETER	0.43-1.15 in
MATERIAL	Santoprene
SPECIAL FEATURES	Watertight locking plug

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - L1630PW Arrow Hart watertight locking plugs, connectors and receptacles spec sheet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

© 2026 Eaton. All Rights Reserved.